


SPECIFICATION FOR APPROVAL

1/3



Name:	EMI FILTER	Part No.:	RD2008031F
YBX MODEL:	YB11A1-3A-Q	Customer P/N :	CN22381 & PELB1067

1. PART NUMBER: YB11A1-3A-Q

2. PHYSICAL DIMENSIONS:



SUGGESTED PANEL CUTOUT
(MOUNTING FROM FRONT)



0 ~ 10	±0.3
10 ~ 100	±0.5
100 ~ 150	±0.8
150 ~ 200	±1.0

Drawing by	Checked by	Approved by	Ordering No.	Unit	Rev.	Dimension Limit	Tolerance
R&D 2020.08.18 王官九		R&D 2020.08.18 喻钰钊	YB11A1-3A-Q	mm			
2020-08-18							



Shenzhen yanbixin
technology co.,Ltd

Tel:+86-755-27147102
Fax:+86-755-27147101

<http://www.yanbixinkeji.com>
E-mail:yanbixin@yeah.net

SPECIFICATION FOR APPROVAL

2/3

Name:	EMI FILTER	Part No.:	RD2008031F
YBX MODEL:	YB11A1-3A-Q	Customer P/N :	CN22381 & PELB1067

3. CHARACTERISTICS:

(1) VOLTAGE RATING.....115/250VAC

(2) CURRENT RATING:

A. @ 115VAC.....3A RMS Max.

B. @ 250VAC.....3A RMS Max.

(3) OPERATING FREQUENCY: 50/60Hz

(4) LEAKAGE CURRENT: EACH LINE TO GROUND

A. @ 115VAC/60Hz.....0.3mA Max.

B. @ 250VAC/50Hz.....0.6mA Max.

(5) HIPOT RATING(FOR ONE MINUTE)


A. LINE TO GROUND.....2250VAC

B. LINE TO LINE.....1450VDC

(6) IR: 50M ohm AT 500VDC ANY INPUT OR OUTPUT TO GROUND

(7) TEMPERATURE RANGE: -25°C~+85°C

4. ELECTRICAL SCHEMATIC:



L:2x1.8mH
Cx:0.1μF(X2)
Cy:3300pF(Y2)*2

5. SAFETY COMPLIANCE:

CE :2011NT0616551

CQC :CQC14001104342/CQC19001226449

CB :STIEP-3025

TUV :B0899310001

UL :E471748

Drawing by	Checked by	Approved by	Ordering No.	Unit	Rev.	
R&D 2020.08.18 王官九		R&D 2020.08.18 喻钰钊	YB11A1-3A-Q	mm		
						2020-08-18



Shenzhen yanbixin
technology co.,Ltd

Tel:+86-755-27147102
Fax:+86-755-27147101


<http://www.yanbixinkeji.com>
E-mail:yanbixin@yeah.net

SPECIFICATION FOR APPROVAL


3/3

Name:	EMI FILTER	Part No.:	RD2008031F
YBX MODEL:	YB11A1-3A-Q	Customer P/N :	CN22381 & PELB1067

6.Label:



7.Carton Label:



Drawing by	Checked by	Approved by	Ordering No.	Unit		
			YB11A1-3A-Q	mm	Rev.	
					2020-08-18	



Shenzhen yanbixin
technology co.,Ltd

Tel:+86-755-27147102
Fax:+86-755-27147101

<http://www.yanbixinkeji.com>
E-mail:yanbixin@yeah.net