

AC300023 - ZD AC Induction Motor



Part Number: AC300023

Summary:

This compact 80mm frame, 3-phase, 110/220 VAC, 4-Pole Induction Motor (ZD Motor 4IK25A-S) is rated for 25 Watts at continuous duty. At 1,300 RPM it draws 250mA and produces 0.19 Nm of torque. This motor has been certified for use with all dsPIC33E/F ACIM motor control application notes using the dsPICDEM MCHV-2 and MCHV-3 Development Systems (DM330023-2, DM330023-3). Orders [View More](#)





Product Features

3-phase, 110/220VAC, 25 Watt 4-Pole Induction Motor

Compact 80nm frame

1,300 RPM rated speed draws 250mA and produces 0.19 Nm of torque

For use with dsPIC33E/F ACIM motor control application notes

For use with the dsPICDEM MCHV-2 and MCHV-3 Development Systems (DM330023-2, DM330023-3)

