



5 kV, 10 kV and 15 kV Test Lead Selection Chart

Supplied as standardOptional

Leads supplied as standard and optional

10 kV Insulation 15 kV
Testers Insulation Testers

	POW	er on	1001 200	u Selectio								lest			lesters
Clip type	Clip capacity	HV Plug	Cat. No. on datasheet	Cat. No. New (if applicable)	Description	Safety CAT rating	BM15	МЈ15	MIT515	MIT525	S1-568	MIT1025	S1-1068	MIT1525	S1-1568
Medium test clip		2"50 mm	1002-531	1008-022	3m (10ft), 6 kV MEDIUM insulated clip, set of 3	CATIV 600V	•	•	•	•	•		•		
	18mm		1002-641		5m (16ft), 6 kV MEDIUM insulated clip, set of 3	CATIV 600V									
			1002-642		8m (26ft), 6 kV MEDIUM insulated clip, set of 3	CATIV 600V									
			1002-643		10m (33ft), 6 kV MEDIUM insulated clip, set of 3	CATIV 600V									
			1002-644		15m (50ft), 6 kV MEDIUM insulated clip, set of 3	CATIV 600V									
			1005-262		3m leadset (x 3, red, blue, black), medium insulated clips	CATIV 600V								•	
		3″ 75 mm 15 kV	1005-263		10m leadset (x 3, red, blue, black) , medium insulated clips	CATIV 600V								-	
Large test clip 10 kV			1002-534	1007-311	3m (10ft), 10 kV LARGE insulated clip, set of 3	CATIV 600V							•		
		2"50 mm	1002-645		5m (16ft), 10 kV LARGE insulated clip, set of 3	CATIV 600V									
	34mm		1002-646		8m (26ft), 10 kV LARGE insulated clip, set of 3	CATIV 600V									
			1002-647		10m (33ft), 10 kV LARGE insulated clip, set of 3	CATIV 600V									
			1002-648		15m (50ft), 10 kV LARGE insulated clip, set of 3	CATIV 600V									4
Large test clip 15 kV	38mm		1005-259		5m leadset (x 3, red, blue, black) , large insulated clips	CATIV 1000V									
		3" 75 mm 15 kV	1005-260		10m leadset (x 3, red, blue, black) , large insulated clips	CATIV 1000V									
			1005-261		15m leadset (x 3, red, blue, black) , large insulated clips	CATIV 1000V									
Compact clip		2″50 mm	8101-181	NLA	3m (10ft), BARE COMPACT clip, set of 3	NONE									
			8101-182	NLA	8m (26ft), BARE COMPACT clip, set of 3	NONE									
			8101-183	NLA	15m (50ft), BARE COMPACT clip, set of 3	NONE									
Compact clip	18mm		6220-835		3m (10ft), BARE COMPACT clip, 5 kV SCREENED black lead, 3 clips, 2 leads	NONE									
			6311-080		15m (50ft), BARE COMPACT clip, 5 kV SCREENED black lead, 3 clips, 2 leads	NONE									
			6220-834		3m (10ft), BARE COMPACT clip, 10 kV SCREENED black lead, 3 clips, 2 leads	NONE									
			6220-861		10m (33ft), BARE COMPACT clip, 10 kV SCREENED black lead, 3 clips, 2 leads	NONE	0								
			6220-833		15m (50ft), BARE COMPACT clip, 10 kV SCREENED black lead, 3 clips, 2 leads	NONE									
Large test clip 15 kV		3" 75 mm 15 kV	1005-266		3m (9.8ft) Leadset, 15kV Screened, large insulated clips	CATIV 1000V									
			1005-267		10m (33ft) Leadset, 15kV Screened, large insulated clips	CATIV 1000V									
	38mm		1005-268		15m (49ft) Leadset, 15kV Screened, large insulated clips	CATIV 1000V									
			1005-269		20m (66ft) Leadset, 15kV Screened, large insulated clips	CATIV 1000V									
1 kV un-fused	20mm	2″ 50 mm	6220-822		3m (10ft), 1kV insulated probe and clip set for CONTROL CIRCUIT TESTING, set of 2	Clip = CATIII Probe = CATIV 600V	-	-	_	-	_	-	_		
		3" 75 mm 15 kV	1005-264		3m (10ft), 1kV insulated probe and clip set for CONTROL CIRCUIT TESTING, set of 2	Clip = CATIII Probe = CATIV 600V									
1 kV un-fused	20mm	2″50 mm	1002-913		1.25m (4ft) 1kV insulated FUSED probe and clip set for <1 kV voltage measurements, set of 2.	CATIV 600V			-	-	-	-	_		
		3″ 75 mm 15 kV	1005-265		1.25m (4ft) 1kV insulated FUSED probe and clip set for <1 kV voltage measurements, set of 2.	CATIV 600V								-	



5_10_15kV_Leads_BR_US_V01
The word 'Megger' is a registered trademark
Copyright © 2017
2621 Van Buren Ave
Norristown, PA 19403
T: 610-676-8500
F: 610-676-8625