



Snap Fit Bushing - Panel Thickness Range 0.8 - 3.2 mm | 0.031 - 0.125 in ; Approximate Cable Holding Diameter 14.3 mm | 0.562 in

Item code: **22MP06879W**

Nylon Open Snap Fit Bushing holds up to 14.3 mm | 0.562 in diameter bundles while creating a smooth, insulated opening. The split design easily snaps into 17.4 mm | 0.687 in holes in panels up to 3.2 mm | 0.125 in thick.

Specifications

Approximate Cable Holding Diameter	0.562 in
---	----------

Compatible Hole Diameter	0.687 in
Head Diameter	0.781 in
Inside Diameter	0.562 in
Maximum Operating Temperature	185 °F
Maximum Panel Thickness	0.125 in
Minimum Operating Temperature	-40 °F
Minimum Panel Thickness	0.031 in
Operating Temperature Range	-40 - 185 °F
Overall Height	0.406 in
Panel Thickness Range	0.031 - 0.125 in
Bushing Type	Closed
Color	White
Full Material	Nylon 6
Material	Nylon
Material Flammability Standard	UL94 V-2
Open/Closed	Open
Special Features	Heat-Stabilized