



Image is for illustrative purpose only

**Cable Clamp - Compatible Cable
Diameter Range - 9.5 mm | 0.375 in;
Operating Temperature Range - -40 - 85
°C | -40 - 185 °F; Black**

Item code: **22CC50G0375B**

This Black UL94 V-2 rated nylon loop clamp is screw mounted for a secure application. Bundle may not be removed without the screw being removed. Maximum bundle diameter is 9.5 mm | 0.375 in. It is 6.4 mm | 0.250 in wide with a 6.4 mm | 0.250 in diameter hole.

Specifications

Compatible Cable Diameter Range	0.375 in
Hole Diameter	0.250 in
Compatible Screw Sizes (All)	1/4, M6
Operating Temperature Range	-40 - 185 °F
Overall Width	0.500 in
Type	1
Style	P-Clip
Material	Nylon
Adjustability	Fixed
Color	Black
Fitting Style	Clamp
Full Material	Nylon 6/6
Material Flammability Standard	UL94 V-2
Mounting Method	Screw