

Han shielded module basic, female



Part number	09 14 027 3121
Specification	Han shielded module basic, female
HARTING eCatalogue	https://b2b.harting.com/09140273121

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Modules
Series	Han-Modular [®]
Type of module	Han [®] Shielded module basic
Description of the module	With 180° shielding element

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	27
Additional contacts	+ shielding
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.09 0.52 mm²
Rated current	4 A
Rated voltage	32 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 +125 °C
Mating cycles	≥500



Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	EN 60664-1
	IEC 61984

Commercial data

Packaging size	1
Net weight	0.01 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440218 Module for industrial connectors (data)