



TECHNICAL INFORMATION

Watts:	40
Lumens:	3200
Input Power:	AC:200-240V, 50Hz
Long Life:	30,000 Hours
Unit Color:	Silver
Body Type:	Aluminium Alloy
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	120°
Color:	6400K
Dimension:	1200x70x60mm
Linkable:	Upto 12 Meters

RECESSED LINEAR LIGHTS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 603 - 1410 1246

[View more details](#)



FEATURES

- Recessed linear lights with a long lifespan of 30,000 hours
- Robust Aluminium body
- Linkable up to 12 meters using connectors
- Multiple connector options (Connectors not included)
- Excellent heat dissipation
- Suitable for commercial and residential applications

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs):	1.7
Unit CBM:	0.3584
Dimension:	1200x70x60mm

MASTER BOX PACKAGING

Box Qty:	12
Qty Per Pallet:	192
Length (Box) mm:	700
Width (Box) mm:	400
Height (Box) mm:	1280

LISTING DETAILS

Commodity Code:	9405403990
EanCode:	3800157639880