

# PRODUCT DATASHEET

## LED BULKHEAD 6 W 4000 K BK

LED BULKHEAD | Wall and ceiling luminaires



---

### AREAS OF APPLICATION

- Outdoor
- Basements, garages, warehouses

---

### PRODUCT BENEFITS

- Easy and quick installation
- Energy-efficient thanks to LED technology

---

### PRODUCT FEATURES

- Bright and functional outdoor LED luminaires
- Type of protection: IP54



## TECHNICAL DATA

### Electrical data

Nominal wattage	5.50 W
Operating mode	Mains voltage
Nominal voltage	220...240 V
Mains frequency	50/60 Hz


### Photometrical data

Color temperature	4000 K
Color rendering index Ra	≥80
Light color (designation)	Cool White
Luminous flux	450 lm
Luminous efficacy	76 lm/W

### Light technical data

Beam angle	120 °
------------	-------

### Dimensions & weight



Length	117.0 mm
Width	168.0 mm
Height	70.0 mm
Product weight	175.00 g

### Colors & materials

Body material	Polycarbonate (PC)
Product color	Black
Housing color	Black
Cover material	Acrylonitrile butadiene styr

## Temperatures &amp; operating conditions

Ambient temperature range	-20...+40 °C
---------------------------	--------------

## Lifespan

Number of switching cycles	100000
Lifespan	20000 h

## Additional product data

Mounting type	Surface
Mounting location	Wall

## Capabilities

Dimmable	No
Type of connection	Screw terminal
LED module replaceable	Not replaceable

## Certificates &amp; standards

Protection class	II
Type of protection	IP54
Standards	CE/EAC/REACH/ROHS

## EQUIPMENT / ACCESSORIES

- Complete mounting and connecting accessories included

## LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075271647	Folding carton box 1	78 mm x 124 mm x 177 mm	202.00 g	1.71 dm <sup>3</sup>
4058075271654	Shipping carton box 8	327 mm x 263 mm x 196 mm	1924.00 g	16.86 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.