

PRODUCT DATASHEET

LED BULKHEAD 11 W 4000 K WT

LED BULKHEAD | Wall and ceiling luminaires



AREAS OF APPLICATION

- Outdoor
- Basements, garages, warehouses

PRODUCT BENEFITS

- Easy and quick installation
- Energy-efficient thanks to LED technology

PRODUCT FEATURES

- Bright and functional outdoor LED luminaires
- Type of protection: IP54



TECHNICAL DATA

Electrical data

Nominal wattage	11.00 W
Operating mode	Mains voltage
Nominal voltage	220...240 V
Mains frequency	50/60 Hz


Photometrical data

Color temperature	4000 K
Color rendering index Ra	≥80
Light color (designation)	Cool White
Luminous flux	800 lm
Luminous efficacy	76 lm/W

Light technical data

Beam angle	120 °
------------	-------

Dimensions & weight



Length	216.0 mm
Width	143.0 mm
Height	79.0 mm
Product weight	245.00 g

Colors & materials

Body material	Polycarbonate (PC)
Product color	White
Housing color	White
Cover material	Acrylonitrile butadiene styr

Temperatures & operating conditions

Ambient temperature range	-20...+40 °C
---------------------------	--------------

Lifespan

Number of switching cycles	100000
Lifespan	20000 h

Additional product data

Mounting type	Surface
Mounting location	Wall

Capabilities

Dimmable	No
Type of connection	Screw terminal
LED module replaceable	Not replaceable

Certificates & standards

Protection class	II
Type of protection	IP54
Standards	CE/EAC/REACH/ROHS

EQUIPMENT / ACCESSORIES

- Complete mounting and connecting accessories included

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075271661	Folding carton box 1	86 mm x 150 mm x 225 mm	282.00 g	2.90 dm ³
4058075271678	Shipping carton box 6	315 mm x 273 mm x 245 mm	1982.00 g	21.07 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.