



**Battery Charger** 

CE-BC 4 M

Item No.: 1002225

Ident No.: 11018

Bar Code: 4006825640311

The Einhell CE-BC 4 M battery charger is an intelligent system with a multi-stage charging cycle and monitoring by a microprocessor controller. It is suitable for all standard 12 V vehicle batteries. The trickle charge function reduces the stress on the battery being charged & extends its service life, especially for seasonal vehicles. There is a recondition mode to enable discharged batteries to be regenerated. Protection against overcharging, shortcircuit, swapped poles & protection against dust & water jets provide reliable protection for the device. The charger has fully insulated pole clamps. The LCD battery voltage & charge status indicator shows the status of the battery at a glance.

## Features & Benefits

- Intelligent battery charger with microprocessor controller
- Multi-stage charging cycle,controlled/monitored by microprocessor
- Universal battery charger for various battery types
- For gel, AGM, zero and low maintenance lead-acid batteries
- Protection class IP65: Dustproof and protected against water jets
- Trickle charge function for a continuously ideal charge status
- For vehicles with long idle times (convertibles/motorcycles)
- Charging provides extended battery life
- Winter charging mode for outdoor temperatures below 5°C
- Recondition mode for charging deeply discharged batteries
- Power supply mode
- LCD battery voltage and charging progress display
- El. protection against overcharging, short-circuit, swapped poles
- Fully insulated battery clamps
- Suspension eyelet for mounting to the wall

## **Technical Data**

- Mains supply 220-240 V | 50 Hz

- Charging voltage

- Suitable for batteries (from min. Ah to 3-120 Ah

max. Ah):

- Charging current Min. (arith./eff.) - Max.1 / [-] - 4 / [-] A (arith./eff.) on 12 V d.c.

## **Logistic Data**

- Product weight 0.36 - Gross weight single packaging 0.56

- Dimensions single packaging 148 x 68 x 244 mm

- Pieces per export carton 12 Pieces - Gross weight export carton 7.3 kg

- Dimensions export carton 415 x 310 x 265 mm - Container quantity (20"/40"/40"HC) 8736 | 18816 | 23520



















