

Mid Span Slit & Ring Tools | Data Sheet



These **PATENTED** slit and ring tools are designed to open fiber jackets and loose buffer tubes to provide easy fiber access. One side of the tool slits fiber jackets and loose buffer tubes, the opposite side rings fiber jackets and loose buffer tubes. All this is done without damage to the fiber. Blades are replaceable. Note: MS-326 is designed for cables used in ducts and microducts.

Simple to use:

- Select the correct groove. Grooves marked with the recommended cable size
- Place the cable in the groove to be used
- Note: The arrow on the top of the tool indicates the pulling direction and the line indicates the blade location
- Close the tool making sure lock is engaged and pull to slit the cable
- For ring operation use ring side of tool and repeat steps above, instead of pulling rotate the tool 3-6 times to ring the cable

| SPECIFICATIONS | MS-526 | MS-426 | MS-336 | MS-326 | MS-316 | MS-306 |
|--------------------------|---|--|--|--|---|--|
| DESCRIPTION | Mid Span Slit & Ring Tool (10.2 mm-18.2 mm) | Mid Span Slit & Ring Tool (5.8 mm-12 mm) | Mid Span Slit & Ring Tool (7.9-8.2 & 10.7-11.0 mm) | Mid Span Slit & Ring Tool (5 mm-10 mm) | Mid Span Slit & Ring Tool (2.9 mm-6.8 mm) | Mid Span Slit & Ring Tool (1.2 mm-3.3 mm) |
| NO. OF PRECISION GROOVES | 8 (4 Slitting, 4 Ringing) | 8 (4 Slitting, 4 Ringing) | 8 (4 Slitting, 4 Ringing) | 10 (5 Slitting, 5 Ringing) | 10 (5 Slitting, 5 Ringing) | 12 (6 Slitting, 6 Ringing) |
| GROOVE SIZES | 10.2 mm 12.2 mm 15.8 mm 18.2 mm | 5.8-6.4 mm 7.8-8.4 mm 9.8-10.4 mm 11.2-12 mm | 7.9-8.2 10.7-11.0 mm | 5.0-5.6 mm 6.0-6.6 mm 7.2-7.8 mm 7.8- 8.4 mm 9.4-10 mm | 2.9-3.6 mm 3.6-4.4 mm 4.4-5.2 mm 5.2- 6.0 mm 6.0-6.8 mm | 1.2-1.5 mm 1.5-1.8 mm 1.8-2.1 mm 2.1-2.5 mm 2.5-2.9 mm 2.9-3.3 mm |
| CABLE DIAMETERS | 10.2 mm-18.2 mm | 5.8 mm-12 mm | 7.9 mm-11 mm | 5 mm-10 mm | 2.9 mm-6.8 mm | 1.2 mm-3.3 mm |
| CABLE TYPE | Corning Altos® with FastAccess® | Thick-walled jackets (up to 2.0 mm thick) | Corning's Minixtend HD 288 and 432 | Thin-walled Jackets | Outer Jackets, Loose Buffer Tubes | Outer Jackets, Loose Buffer Tubes |

Replacement Cartridges



| JONARD PART # | DESCRIPTION |
|---------------|----------------------------------|
| MS-306RB | Replacement Blades for MS-306 |
| MS-316RB | Replacement Blades for MS-316 |
| MS-336RB | Replacement Blade Set for MS-336 |
| MSB-5010 | Replacement Blades for MS-326 |
| MS-426RB | Replacement Blades for MS-426 |
| MS-526RB | Replacement Blades for MS-526 |

MADE FOR LIFE®