

A-2060DD-EB

The A-2060DD-EB is a high cost-performance mixer power amplifier suited for broadcasting paging or background music in schools, offices, shops, factories, mosques, churches and large rooms.



Article number A-2060DD-EB 1CE
Alternative products: A-2060D-EB

Specifications

Power source	220 - 240 V AC, 50 / 60 Hz
Rated output	60 W
Frequency response	50 Hz - 20 kHz (± 3 dB)
Distortion	< 1 % (at 1 kHz, 1/3 rated output power)
S/N ratio	60 dB (or more)
Number of channels	1
Connectable microphones	3
Inputs	MIC 1: -60dBV, 600 Ohm, balanced, 5-pin DIN equivalent, phantom power selectable, + 21V Mic 2-3: -60dBV, 600 Ohm, balanced, phone jack AUX 1-2: -20 dBV, 10 kOhm, unbalanced RCA pin jack
Control input	Mute: via DIN jack
Outputs	Speaker: balanced (floating) / Rec out: 0 dBV, 600 Ω , unbalanced, RCA Pin Jack
Dimensions (W x H x D)	420 x 100,6 x 280,3 mm
Dimensions (ϕ x D)	x 280,3 mm
Finish	ABS resin, Steel plate, black,



A-2000D Series

A-2060DD-EB

Appearance