

3108

Super Duty Air Die Grinder



For the ultimate performance and versatility in a lightweight package with superior manoeuvrability, the 3108 is the perfect choice. With all ball bearing constructions, you get longer lasting life and advanced durability, along with a composite grip for superior ergonomics and comfort. Use this powerful die grinder in a various applications including porting, weld braking, deburring, polishing, and grinding, just to name a few.

Features

- Powerful 1/3 horsepower motor
- Lightweight yet durable design
- All ball bearing construction
- Safety release throttle
- Positive grip 1/4" capacity collet chuck
- Ergonomic and durable composite housing

Model	Av. Air Consumption cfm (l/min)	Air Inlet NPTF in.	Strokes per Min.	Sound dBA (Pressure/Power)	Performance Rating
3108	3 (85)	1/4	N/A	92/103	Super Duty

@ Load cfm (l/min)	Length in. (mm)	Min Hose Size in. (mm)	Collet Size in.	Free Speed (rpm)	Weight lbs. (kg)	Rated Power hp (kW)
18 (510)	6.75 (171)	3/8 (10)	1/4	25,000	1.27 (.58)	.33 (.25)