

363192

	DeWALT	
Supplier		
Model number	DC385KB	DC305KL
Voltage	18	36
No load strokes/min	3000	0-3000
Stroke length (mm)	28.6	29
Cutting capacity steel pipe (mm)	100	100
Cutting capacity wood (mm)	265	280
Battery	2 x 2.6Ah Ni MH	2 x 2.2Ah Li-ion
Weight (kg)	3.7	3.81
Order code	No Order Code	135-2944
Price		
each		