

Photovoltaic connector - PV-FT-C4F-C-6-130-BU-00 - 1158448


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Photovoltaic connector, Range of articles: SUNCLIX, Photovoltaic connector, housing material: PPE, color: black, Connection method: Crimp, Type of contact: Socket



Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 063151 163976
GTIN	4063151163976
Weight per Piece (excluding packing)	22.220 g

Technical data

General

Design	Socket
Degree of pollution	2
Rated surge voltage (III/3)	16 kV
Rated voltage	1500 V
Rated current (6.0 mm ²)	40 A

Material

Color	black
Cable gland material	PA

Connection data

Connection method	Crimp
Type of contact	Socket

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

