

Tradesman™ Knives



- Blades and tools made from Stainless Steel hardened to 53-56° Rockwell C
- Ergonomically shaped handles moulded from Zytel glass-reinforced nylon & feature a sure-grip design for additional safety in demanding conditions

Specifications:

- TM1** – Hawkbill knife with lockblade, heavy duty shackle. Closed length 100mm
- TM2** – Screwdriver knife with spear point and locking screwdriver/wire stripper blades, heavy duty shackle. Closed length 92mm
- TM3** – Master tri-blade with spear point, hawkbill and locking screw driver/wire stripper blades, heavy duty shackle. Closed length 92mm
- TM4** – Pocket size general utility knife with clip, awl & scalloped sheepfoot blades. Closed length 83mm
- TM5** – Dual edge lockblade knife with single scallop-edged clip blade. Closed length 100mm
- TM7** – Mini lockblade knife with single clip blade, heavy duty shackle. Closed length 56mm
- TM8** – All-purpose shear with serrated blade, wire cutter, jar opener, bottle opener, lid lifter and screwdriver. Polypropelene. Closed length 208mm
- TM9** – Sheepfoot lockable knife with single blade, heavy duty shackle. Closed length 100mm
- TM10** – Scallop-edged lockblade knife, heavy duty shackle. Closed length 100mm
- TM11** – Electrician's knife with dual-edge locking spear point blade and wire/insulation stripper, heavy-duty shackle. Closed length 105mm
- TM12** – Multi-purpose workshop knife with spear blade and locking screw driver/wire stripper/file blade. Closed length 100mm
- TM13** – Multi-purpose tri-blade knife with spear blade, hawkbill and locking screw driver/wire stripper/nail file. Closed length 100mm

HAT544

Mftrs. List No.	Order Code	Price Each
TM1	725-5755	
TM2	725-5767	
TM3	725-5779	
TM4	725-5780	
TM5	725-5792	
TM7	725-5809	
TM8	725-5810	
TM9	725-5822	
TM10	725-5834	
TM11	725-5846	
TM12	725-5858	
TM13	725-5860	