Note: This datasheet may be out of date.

Please download the latest datasheet of LQP03HQ36NJ02# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=LQP03HQ36NJ02%23

"#" indicates a package specification code.

LQP03HQ36NJ02D

Size Code 0603 (0201) in mm (in inch), Higher Q



















< List of part numbers with package codes >

LQP03HQ36NJ02D

LQP03HQ36NJ02B

LQP03HQ36NJ02J



Appearance & Shape











References

Packaging	Specifications	Standard Packing Quantity
D	180mm Paper Tape	15000
В	Bulk(Bag)	500
J	330mm Paper Tape	50000

Mass (typ.)		
1 piece	0.22mg	

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



LQP03HQ36NJ02D

Note: This datasheet may be out of date. Please download the latest datasheet of LQP03HQ36NJ02# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=LQP03HQ36NJ02%23

"#" indicates a package specification code.



Specifications

I size	0.6±0.03mm
L Size	0.0±0.03fffff
W size	0.3±0.03mm
T size	0.4±0.02mm
Size code inch (mm)	0201 (0603)
Inductance	36nH±5%
Inductance Test Frequency	300MHz
Rated current (Itemp) (Based on Temperature rise)	150mA
Max. of DC resistance	2Ω
Q(min.)	12
Q Test Frequency	300MHz
Self resonance frequency (min.)	1500MHz
Operating Temperature Range(Self-temperature rise is not included)	-55°C to 125°C
Series	LQP03HQ_02

2 of 3

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Note: This datasheet may be out of date. Please download the latest datasheet of LQP03HQ36NJ02# from the official website of Murata Manufacturing Co., Ltd.


http://www.murata.com/en/products/productdetail?partno=LQP03HQ36NJ02%23

"#" indicates a package specification code.




Characteristic Data

LQP03HQ36NJ02D



Inductance - Frequency Characteristics



Q-Frequency Characteristics

3 of 3

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

