

This Drawing is the property of J.S.T.(U.K.) Ltd.
It must not be copied or used for manufacturing
without written permission from J.S.T.(U.K.) Ltd.

**UNCONTROLLED
CUSTOMER ISSUE**

Page 1 of 2



CS-28N002V0750NF	28N002V0750NF	PA66	UL94V-0	Natural	65	--	
CS-28N502STY	28N502STY	PA46	UL94V-2	Black	150	--	
CS-28N002STY	28N002STY	PA46	UL94V-2	Natural	150	--	
CS-28N502V0	28N502V0	PA68	UL94V-0	Black	140	E172855 (M)	
CS-28N002V0	28N002V0	PA68	UL94V-0	Natural	140	E172855 (M)	
CS-28NGR02	28NGR02	PA66	UL94V-0	Grey	130	E172855 (M)	
01019 BLUE	28N602	PA66	UL94V-2	Blue	130	E172855 (M)	
01019 BLACK	28N502	PA66	UL94V-2	Black	130	E172855 (M)	
01019 RED	28N302	PA66	UL94V-2	Red	130	E172855 (M)	
01019 GREEN	28N402	PA66	UL94V-2	Green	130	E172855 (M)	
01019 YELLOW	28N202	PA66	UL94V-2	Yellow	130	E172855 (M)	
01019	28N002	PA66	UL94V-2	Natural	130	E172855 (M)	
JST Part Number	Mfg Number	Material	Flame Class	Colour	Max Operating Temp (°C)	UL Card No.	//

Revision Record	Add; Yellow, Blue, Green, Grey	14.07.06
	Add; 28N002V0750NF	28.11.05
	Amend temp rating for all materials	01.12.04
	Add suffix; 002V0	30.09.03
	Modification Detail	Date
		

Part Description & General Details:		
Housing for 2.8 (.110) receptacle. Applicable JST terminal; STO-**(*)-110*(-*)		
Series:	28 Series	
Drawing Ref:	CS28N002-041094	
Issues by:	ZG	23.08.02
Approved by:	AR	23.08.02

This Drawing is the property of J.S.T.(U.K.) Ltd.
It must not be copied or used for manufacturing
without written permission from J.S.T.(U.K.) Ltd.

**UNCONTROLLED
CUSTOMER ISSUE**



Revision Record	Add; Yellow, Blue, Green, Grey	14.07.06
	Add; 28N002V0750NF	28.11.05
	Amend temp rating for all materials	01.12.04
	Add suffix; 002V0	30.09.03
Modification Detail		Date

JST

Part Description & General Details:

Housing for 2.8 (.110) receptacle.
Applicable JST terminal; STO-**(*)-110*(-*)

Series:	28 Series	
Drawing Ref:	CS28N002-041094	
Issues by:	ZG	23.08.02
Approved by:	AR	23.08.02