

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2059792071](#)
Status: **Active**
Overview: [Micro-One Wire-to-Board Connector System](#)
Description: [Micro-One Wire-to-Board Receptacle Housing, 2.00mm Pitch, Single Row, with Independent Secondary Lock \(ISL\), 7 Circuits](#)

Documents:	
3D Model	Application Specification 2059790000-AS-000 (PDF)
Drawing (PDF)	Packaging Specification 2059799200-SPK-200 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification 2059790000-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	205979
Application	Power, Wire-to-Board
Overview	Micro-One Wire-to-Board Connector System
Product Name	Micro-One
UPC	191130093885

Physical	
Circuits (maximum)	7
Color - Resin	Black
Gender	Female
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyamide
Net Weight	624.510/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers	
Application Specification	2059790000-AS-000
Packaging Specification	2059799200-SPK-200
Product Specification	2059790000-PS-000
Sales Drawing	2059790000-SD-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[205979](#) Series

Mates With
Micro-One Vertical Header [205971](#) . Micro-One Right-Angle Header [205972](#)

Use With
Micro-One Female Crimp Terminal [56134](#)