BNC Plug






Specifications:

Bodies : Brass per JIS-C3604 Centre Contact : Brass per JIS-C3604

Insulation : PTFE per ASTM D1457 and ASTM D1710

Connector interface per MIL-STD-348A Part to be clean and free of burrs

Diagram



No.	Description	Material	Finish
1	Shell	Zinc	Nickel 100μ" Min.
2	Body	Brass	
3	Insulation	PTFE	None
4	Gasket	Rubber	
5	Washer	Brass	Nickel 100µ" Min.
6	Insulation	PTFE	None
7	Spring Washer	SK-5	Nickel 100μ" Min.
8	Washer	Brass	
9	Braid Clamp		
10	Gasket	Rubber	None
11	Washer	Brass	Nickel 100μ" Min.
12	Nut		
13	Centre Contact		Gold

Part Number Table

Description	Part Number
RF / Coaxial Connector, BNC Coaxial, Straight Plug, Solder, 50Ω, RG174, Brass	MP-13-01-3 TGZ RG174U

Dimensions: Millimetres (Inches)

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

