

MERKAVA GM-15

The Merkava GM-15 gaming mouse is an excellent functional weapon for games of various difficulty levels. It features the latest Sunplus 6662 optical sensor, convenient cable length for uninterrupted signal transmission, ergonomic shape, and anti-slip coating to help make even the longest gaming session engaging and comfortable. You can customize the functions of 12 buttons and store your settings reliably. Vivid RGB backlight helps create an atmosphere that matches the mood of your favorite game. The mouse has a wide DPI switching range from 400 to 12000. It is durable and comfortable, so it is perfect for both fun and everyday work on the computer.



(1.65 m











Onboard







FEATURES

- Sensor Sunplus 6662
- 12 programmable buttons
- Macro-buttons
- 6 default DPI levels 400/800/1600/2400/3200/5000
- Maximum DPI 12000
- Buttons lifespan up to 10 million clicks
- Ultra-weave USB cable with ferrite ring, 1.65m
- Weight adjustment system (3x3.5g)

- Enhanced RGB system of backlight
- Scanning frequency: 6000 FPS
- Polling rate: 125/250/500/1000 Hz
- Max acceleration: 22.5G
- Max moving speed: 66 ips
- Additional software to setup the settings
- Macro functions
- Onboard memory to save the settings

CND-SGM15 | 5291485007461



MERKAVA GAMING MOUSE GM-15

EXCELLENT PARAMETERS FAST RESPONSE SPEED

Optimized for gaming, this mouse has a maximum movement speed of 66 ips and 22.5G acceleration. An adjustable polling rate and 6,000fps scan rate ensure excellent responsiveness across the entire DPI range.

EXTENSIVE CUSTOMIZATION OPTIONS SET UP THE SOFTWARE ACCORDING TO YOUR PREFERENCES

The mouse software has been designed to give you unlimited customization options for any game of any genre. You can easily create a player profile, assign macros, change button mapping, responsiveness, or DPI.

UNINTERRUPTED SIGNAL BRAIDED CABLE WITH FERRITE FILTER

The braided cable and ferrite filter suppresses high-frequency noise and improves signal speed and clarity. Rugged and maneuverable, it is an integral part of a quality mouse.

12 PROGRAMMABLE BUTTONS MULTI-FUNCTION KEYS WITH EASY CONFIGURATION

The mouse driver allows you to customize macros and reassign button functions to your game or game character's specifics. Feel the convenience of full customization and enjoy high gaming performance!

MAXIMUM PLAYABILITY SIDE BUTTONS

Additional side buttons located on the left allow you to use your thumb for shooting or other game actions. Of these, the bottom 4 numbered ones can serve as macro buttons. This significantly increases the level of comfort in challenging games and reduces the fatigue of hand muscles. You can also customize side buttons for frequent actions outside of gaming activities, like navigating documents or adjusting the volume.

WEIGHT CUSTOMIZATION ADDITIONAL WEIGHTS INCLUDED

The mouse has an adjustable weight system that includes 3 weights of 3.5 grams each. This allows you to adjust the mouse's weight so that it feels maximally comfortable and matches the dynamics of the chosen game as best as possible.

OPTIMAL DPI RANGE SENSOR SUNPLUS 6662

This high-precision optical sensor offers an extended sensitivity range from 400 to 12,000 DPI. The mouse driver allows you to set the optimal value for the game in increments of 200 DPI. Change resolution on the fly and enjoy precise mouse movement!