

NYS373

Phono plug, black housing, gold plated contacts, rubber anti-kink boot, chuck type strain relief, cable O.D. 3.5 - 6.1 mm





Article Variations

Article Name	Details	Packaging
NYS373-0	Black color coding	
NYS373-2	Red color coding	
NYS373-4	Yellow color coding	
NYS373-5	Green color coding	
NYS373-6	Blue color coding	
NYS373-9	White color coding	

Technical Information

Product

Title	NYS373
Connection Type	Phono ("RCA/Cinch")

Electrical

Contact Resistance	≤10 mΩ
Insulation Resistance	>2000 MΩ(Initial)
Rated Voltage	0.5 VAC

Mechanical

Insertion and Withdrawal Force	5-20N
Lifetime	>5000 Mating Cycles

Material

Pin	Brass
Housing	Copper
Housing	Zinc
Boot	PVC
Ground Contact	H62
Chuck	PA6
Color dividing ring	Rubber
Elastic clamp	ABS
Pin	Gold
Housing	Gold
Ground Contact	Gold
Housing	Black