

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192050006

Status:

Active

Overview:

Splices

Description:

VersaKrimp Parallel Splice for 6 AWG Wire

Documents:

Drawing (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E32244

General

Product Family

Splices

Series

19205

Crimp Quality Equipment

Yes

Overview

Splices

Product Name

Parallel, VersaKrimp

UPC

800755060850

Physical

Barrel Type

Closed - Brazed

Insulation

None

Material - Metal

Copper

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Net Weight

3.338/g

Packaging Type

Bag

Wire Size AWG

6

Material Info

Engineering Number

E-361

Reference - Drawing Numbers

Product Specification

PS-19902-011-001, PS-19902-013-001

Sales Drawing

SD-19205-007



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2020)9139-DC (19

Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19205 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

| Global                                                         |           |
|----------------------------------------------------------------|-----------|
| Description                                                    | Product # |
| Manual Putt Pump Hydraulic System, Die set required            | 192860117 |
| Die Set (large) for the HHLS Hydraulic Crimper                 | 192900004 |
| Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals | 192940008 |
| Hydraulic Dieless Crimping Tool                                | 638161700 |

|                    |                  |
|--------------------|------------------|
| PremiumGrade Hand  | <u>640013900</u> |
| Crimp Tool for 2-8 |                  |
| AWG Terminals      |                  |
| Square “DIN” style | <u>640037770</u> |
| dies for 6 AWG     |                  |
| Crimp Head for the | <u>640074300</u> |
| AT-200 Pneumatic   |                  |
| Hand Tool          |                  |

This document was generated on 03/04/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**