

HL 1820 S 110 V

Slim, light, tireless.

NEW!
Available

Technical Specifications

Voltage:	110 V
Output:	1.300 W
Temperature:	50 / 400 / 550 °C
Airflow rate:	100 / 200 / 300 l/min
Stages:	3
Highlights:	Hanger, higher durability (+20 %), optimised weight balance
Power cord:	Length: 2,20 m
Motor:	Brush motor
Heating element:	Micanite heating element
Motor lifetime:	600 hours
Accessories:	Use of our standard accessories
Included:	Folded box
Weight of packaging:	Gross: 970g; net: 800g
Dimensions of packaging:	252 x 82,5 x 200 mm
Costums tariff number:	84198998 UL RO
Country of origin:	Romania
Region of origin:	03

