

# HL 1820 S

Slim, light, tireless.

**NEW!**

Available from October 2016

## Technical Specifications

Voltage:	220-230 V, 50/60 Hz
Output:	1.800 W
Temperature:	50 / 400 / 600°C
Airflow rate:	150 / 300 / 500 l/min
Stages:	3
Highlights:	Hanger, higher durability (+20 %), optimised weight balance
Power cord:	Length: 2,20 m
Motor:	Brush motor
Heating element:	Micanite heating element
Motor lifetime:	600 hours
Accessories:	Use of our standard accessories

Included:

Folded box

Weight of packaging:

Gross: 970g; net: 800g

Dimensions of packaging:

252 x 82,5 x 200 mm

Customs tariff number:

84198998 UL RO

Country of origin:

Romania

Region of origin:

03

