

10-Port USB 3.0 Hub with Charge and Sync Ports - 2 x 1.5A Ports

Product ID: ST103008U2C



This 10-port USB 3.0 hub enhances your system's capabilities by providing fast-charging for mobile devices, plus quick access to your USB devices, making it perfect for business or home-office settings.

As a charging station, the hub features two easy-access 1.5 amp charge-and-sync ports, so you can easily fast-charge your smartphones, tablets and other mobile devices. Plus, you can still connect all of your vital peripherals to the remaining data ports. Because the hub supports USB Battery Charging Specification 1.2, you can charge most mobile devices, including Apple devices and Android devices such as the Samsung Galaxy.

Designed for maximum scalability, this 10-port hub boosts your productivity by putting all of your USB devices within easy reach. With USB 3.0 transfer rates up to 5Gbps, it supports high-bandwidth devices such as external hard drive enclosures, flash drives, high-resolution webcams, video cameras, and more.

With its sleek and compact design, you can easily position the USB 3.0 (also known as USB 3.1 Gen 1) hub on your desk or workspace to make your USB devices more accessible. There's also ample space between the USB 3.0 ports, so it's easy to plug and unplug the devices you use the most.

The USB 3.0 hub is multi-platform compatible and is natively supported in virtually all operating systems including Windows and Mac, which makes for an easy setup with no driver installation required.

The ST103008U2C is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Conveniently fast-charge your mobile devices or sync with your computer
- Deploy as a charging station or data hub in hot-desk environments

- Upgrade the capabilities of your desktop or laptop with 10 additional USB 3.0 ports
- Make hard-to-reach USB ports more accessible

Features

- Boost your system's capabilities and turn one USB 3.0 port into ten
- Fast-charge your smartphone or tablet, using two charge-and-sync ports with 1.5A output
- Charge a variety of mobile devices, including Apple and Samsung Galaxy devices, with support for USB Battery Charging Specification 1.2
- Includes a 48W universal power adapter
- Multi-platform compatibility, with no drivers required
- Slim and sleek black enclosure
- Built-in on/off power button
- SuperSpeed USB 3.0 throughput up to 5Gbps
- LED indicators for port status
- Supports plug-and-play, hot-swap, and hot-plugging
- Backward compatible with USB 2.0 and 1.x devices

Prominence

Warranty	2 Years
Description CDW 75 - 1st Line	StarTech.com 10 Port USB 3.0 Hub 10x USB-A w/ 2x Fast Charge - Self Powered

Hardware

USB-C Device Port(s)	No
USB-C Host Connection	No
Fast-Charge Port(s)	Yes
Ports	10
Interface	USB 3.0
Bus Type	USB 3.0

Industry Standards	USB Battery Charging Specification Rev. 1.2
	USB 3.0 - Backward compatible with USB 2.0/1.1
Chipset ID	VIA/VLI - VL812

Performance

Maximum Data Transfer Rate	5 Gbps
Type and Rate	USB 3.0 - 5 Gbit/s

Connector(s)

Connector Type(s)	USB Type-A (9 pin) USB 3.0 (5 Gbps)
	USB 3.0 A (Fast-Charge, 9 pin)

Software

OS Compatibility	OS Independent; No additional drivers or software required
------------------	--

Special Notes / Requirements

System and Cable Requirements	Host computer with an available USB 3.0 port
Note	If connected to a USB 2.0 host port, performance may be limited
	Charge and sync port(s) with a fast-charge icon: If your host computer is turned off, in sleep mode, or disconnected, the hub will disable data sync mode and enable fast-charge mode automatically
	If your host computer is turned on, a charge and sync port will provide a standard charge to a connected device plus simultaneous data sync capabilities

Indicators

LED Indicators	Port status (Blue)
----------------	--------------------

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	1.0 A
Output Voltage	12V DC

Output Current	4 A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	48

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10% ~ 90% RH (Non-condensing)

Physical Characteristics

Color	Black
Form Factor	Desktop
Material	Plastic
Product Length	7.9 in [20.1 cm]
Product Width	2.4 in [60 mm]
Product Height	0.9 in [24 mm]
Weight of Product	5.1 oz [144 g]

Packaging Information

Package Length	7.6 in [19.4 cm]
Package Width	11.5 in [29.3 cm]
Package Height	2.9 in [73 mm]
Shipping (Package) Weight	22.6 oz [639 g]

What's in the Box

Included in Package	10-port USB 3.0 hub with charge & sync ports
	USB 3.0 host cable [80 cm/31.5 in.]



universal power adapter

universal power adapter (NA/JP, UK, EU, ANZ)

****Product appearance and specifications are subject to change without notice.***

