

7-Port USB 3.0 Hub - Desktop or Wall-Mountable Metal Enclosure

Product ID: ST7300U3M



The StarTech.com 7-port USB 3.0 hub is your answer for a durable and compact hub that's ideal for desktop or travel usage.

This hub is perfect for a permanent setup with a desktop computer, with a rugged metal housing that can withstand the wear and tear of daily use. Plus, you can attach it to a surface such as a desktop or wall using the included wall-mount bracket.

The compact size and durability of the hub also make it perfectly portable. When you're on the go, its robust design resists damage that can occur when travelling or from back-and-forth trips from home to office.

The ports on this hub are upright, which makes it perfect for IT professionals or anyone who needs to plug and unplug their USB devices regularly. You have lots of room to grip the connectors, without the worry of oversized plugs taking up too much space and reducing the number of available ports.

With extra USB 3.0 ports, you can increase productivity and connect more devices to your computer, or simply avoid the hassle of swapping connected devices on your port-limited laptop. The hub makes your USB ports more accessible and can easily extend the range of your devices by acting as a mid-point repeater.

The ST7300U3M supports the latest USB 3.0 products including UASP-enabled storage devices. With data transfer speeds of up to 5 Gb per second using SuperSpeed USB 3.0 technology, this high-performance hub is the perfect accessory for your desktop, laptop, MacBook, or UltraBook.

You can also use the hub with older peripherals and computers, with support for USB 2.0 and 1.x devices and no additional drivers or software required for installation.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Deploy in hot desk environments to provide USB hub access for multiple devices
- Connect a wide variety of peripherals at home or in the office, all from a single USB 3.0 connection

Features

- Transfer large files at lightning speed, with throughput support up to 5 Gbps
- Upright port configuration makes plug-in easy, even for oversized USB connectors
- Backward compatibility lets you save money and use with existing USB 2.0 and 1.x devices
- Flexible mounting options, with the included desktop or wall-mount bracket
- Travel friendly, with a compact and rugged metal enclosure
- Plug-and-play and hot-swap compatible

Prominence

Warranty	2 Years
Description CDW 75 - 1st Line	StarTech.com 7 Port USB 3.0 Hub - 7xUSB-A - Mountable, Metal - Self Powered

Hardware

USB-C Device Port(s)	No
USB-C Host Connection	No
Fast-Charge Port(s)	No
Ports	7
Interface	USB 3.0
Bus Type	USB 3.0
Chipset ID	ASMedia - ASM1074


Performance

Maximum Data Transfer Rate	5 Gbps
Type and Rate	USB 3.0 - 5 Gbit/s

Connector(s)



	Connector Type(s)	USB Type-A (9 pin) USB 3.0 (5 Gbps)
		USB Type-B (9 pin) USB 3.0
Software		
	OS Compatibility	OS Independent; No additional drivers or software required
Special Notes / Requirements		
	System and Cable Requirements	Available USB 3.0 port
	Note	If connected to a USB 2.0 host port, performance may be limited
Indicators		
	LED Indicators	Power
		Hub Port Connection
Power		
	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	1.3 A
	Output Voltage	12V DC
	Output Current	3.0 A
	Center Tip Polarity	Positive
	Plug Type	M
	Power Consumption (In Watts)	36
Environmental		
	Operating Temperature	5C to 35C (41F to 95F)
	Storage Temperature	-20C to 50C (-4F to 122F)
	Humidity	20~80% RH
Physical Characteristics		
	Color	Black



Form Factor	Desktop
Material	Aluminum
Cable Length	4.0 ft [1.2 m]
Product Length	4.3 in [11.0 cm]
Product Width	1.7 in [44.0 mm]
Product Height	0.9 in [24.0 mm]
Weight of Product	4.7 oz [133.0 g]

Packaging Information

Package Length	6.7 in [16.9 cm]
Package Width	4.1 in [10.5 cm]
Package Height	4.1 in [10.4 cm]
Shipping (Package) Weight	21.1 oz [599.0 g]

What's in the Box

Included in Package	USB 3.0 Hub
	USB 3.0 A - B Cable - 3.3 ft.
	Wall-Mount Bracket (w/ Screws)
	Rubber Footing Strips
	Universal Power Adapter (NA/JP, EU, UK, ANZ)
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

