



### Overview

Lead time	Usually in Stock
-----------	------------------

### General

Provided equipment	User manual Rack mounting brackets
--------------------	---------------------------------------

### Physical

Cable length	1.98 m
Colour	Black
Depth	7.6 cm
Height	8.9 cm
Net weight	2 kg
Width	43.2 cm

### Input

Network frequency	50/60 Hz
Plug standard	IEC 60320 C14
Number of cables	1
Permissible voltage	220...240 V
Max line current	10 A
Input current limits	10 A
Load capacity	1500 VA
Power factor	0...1
Input voltage	230 V

### Output

Max current draw	10 A
Number of power socket outlets	6 IEC 60320 C13 1 IEC Jumpers
Number of power socket outlets	6

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protection type	Circuit breaker
Power cable length	1.22 m
Efficiency	99 %
Output voltage	230 V

## Conformance

Product certifications	VDE
------------------------	-----

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...15000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

## Packing Units

Package 1 Weight	3.5 kg
Package 1 Height	15.1 cm
Package 1 width	46.3 cm
Package 1 Length	29.5 cm
Number of Units in Package 3	56

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------