

SB 18 L (602317500) Cordless hammer drill

18V 2x2Ah Li-ion; Charger SC 30 (220-240 V / 50 - 60 Hz); metaBOX 145

Order no. 602317500

EAN 4007430327437



Product may differ from image

- Compact cordless hammer drill for universal application areas
- Hammer drill function for drilling in masonry
- Integrated LED work light with night light function for optimal brightness in the work area
- With handy belt hook and bit case which can be fixed either on the right or left side
- With metaBOX, the intelligent solution for transport and storage

Technical data

Characteristics

Type of battery pack	Li-ion
Battery voltage	18 V
Battery pack capacity	2 x 2 Ah
Maximum torque - soft	25 Nm / 221.3 in-lbs
Maximum torque, hard	50 Nm / 442.5 in-lbs
Adjustable torque	1.5 - 6 Nm // 13.3 - 53.1 ft. lbs
Drill-Ø masonry	10 mm / 3/8 "
Drill Ø steel	10 mm / 3/8 "
Drill-Ø soft wood	20 mm / 25/32 "
No-load speed	450 / 1800 rpm
Maximum impact rate	27000 bpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight (including battery pack)	1.6 kg / 3.5 lbs

Vibration

Drilling in metal	2.8 m/s ²
Uncertainty of measurement K	1.5 m/s ²
Impact drilling concrete	21.5 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	89 dB(A)
Sound power level (LwA)	100 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Keyless chuck
Charger SC 30
Charger SC 30
metaBOX 145
Belt hook and bit case
2 Li-Power battery packs (18 V/2.0 Ah)