

**STAB 18 LTX 100 (601003840) Cordless Jigsaw**  
**18V; metaBOX 145 L**

Order no. 601003840  
EAN 4007430324573



Product may differ from Image



- Precise and material-matched sawing due to the variable stroke rate, pendulum stroke and low-lying saw blade guidance with spring support
- Metabo "Quick" for changing saw blades without tools and with automatic ejection
- Top handle with non-slip soft-grip surface
- Selectable shaving blower function ensures free view of cutting line
- With metaBOX, the intelligent solution for transport and storage

## Technical data

### Characteristics

Battery voltage	18 V
Cutting depth wood	100 mm
Cutting depth NF metal	25 mm
Cutting depth sheet steel	10 mm
Swivel range from / to:	- 45 / + 45 °
Pendulum stroke levels	4
Strokes in idle	0 - 2800 rpm
Weight (including battery pack)	2.6 kg

### Vibration

Sawing wood	9.8 m/s <sup>2</sup>
Uncertainty of measurement K	1.5 m/s <sup>2</sup>
Sawing metal	6.5 m/s <sup>2</sup>
Uncertainty of measurement K	1.5 m/s <sup>2</sup>

### Noise emission

Sound pressure level	84 dB(A)
Sound power level (LwA)	95 dB(A)
Uncertainty of measurement K	3 dB(A)

## Scope of delivery

Extraction nozzle  
Protective glass  
Chip guard plate  
Hexagonal wrench  
metaBOX 145 L  
without battery pack, without charger