

W 9-115 (600354380) Angle Grinder
(220-240 V / 50 - 60 Hz); Cardboard box

Order no. 600354380
EAN 4007430244604



Product may differ from Image



- Low fatigue as never before: compact angle grinder with smallest handle circumference in its class for perfect ergonomics
- Longer service life, more power: the Metabo Marathon-motor with patented dust protection, up to 20% more overload capacity and 50% more torque
- Tool-free adjustable guard; twist-proof
- Metabo S-automatic mechanical safety clutch: minimises kick-back to the lowest level when the disc jams unexpectedly - for maximum user safety and swift progress
- Restart protection after power interruption
- Gear housing can be unscrewed, rotated in 90° steps and remounted for left-handed operation or cutting
- Auto-stop carbon brushes to protect the motor

Technical data

Characteristics

Grinding wheel Ø	115 mm
Rated input power	900 W
Output power	550 W
No-load speed	10500 rpm
Revolutions at rated load	7500 rpm
Torque	2.5 Nm
Spindle thread	M 14
Weight (without power cable)	2.1 kg
Cable length	2.5 m

Vibration

Surface grinding	4.9 m/s ²
Uncertainty of measurement K	1.5 m/s ²
Grinding with sandpaper	2.5 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	93 dB(A)
Sound power level (LwA)	104 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Guard
Inner support flange
Nut with two holes
Side handle
Flat-pin spanners