

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2163011212](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead MX150 Female-to-Pigtail, Gold (Au) Plating, 150.00mm Length, 16 AWG, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

| | |
|------------------------|---|
| Product Family | Cable Assemblies |
| Series | 216301 |
| Application | Power, Wire-to-Board, Wire-to-Wire |
| Assembly Configuration | Pre-crimped Lead Only |
| Connector to Connector | MX150 Terminal-to-Pigtail |
| Overview | Off-the-Shelf Pre-Crimped Leads |
| Product Name | MX150 |
| UPC | 195842070820 |

Physical

| | |
|------------------------------|------------------------------|
| Cable Length | 150.00mm |
| Circuits (Loaded) | 1 |
| Color - Resin | Black |
| Gender | Female-Pigtail |
| Material - Metal | High Performance Alloy (HPA) |
| Material - Plating Mating | Gold |
| Net Weight | 3.077/g |
| Packaging Type | Bag |
| Single Ended | Yes |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 2.70mm max. |
| Wire Size AWG | 16 |
| Wire/Cable Type | TXL |

Electrical

| | |
|-------------------------------|---------------|
| Current - Maximum per Contact | Contact Molex |
| Voltage - Maximum | 14V DC |

Material Info

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | 2163011211-000 |
|---------------|----------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[216301](#) Series

Use With

MX150 Dual Row Housing [33472](#) . MX150
Single Row Housing [33471](#) . MX150 Hybrid
Housing [33476](#)