

















## L 8 W/535



Product code 4050300241807

|   |          |
|---|----------|
|    | G5       |
|    | 288.0 mm |
|    | 16.0 mm  |
|   | –        |
| <b>W</b>  | 8.00 W   |
| <b>lm</b>   | –        |
|  | –        |
|  | –        |
|  | 385 lm   |
|  | 385 lm   |
| <b>cd</b>   | –        |
| <b>K</b>  | –        |
| COLOUR  | –        |
| <b>R<sub>a</sub></b>  | ≥50      |
| <b>t</b> [h]  | 5000 h   |
|  | –        |
| <b>V</b>  | –        |
| <b>Hz</b>   | –        |

|   |             |
|---|-------------|
|    | –           |
|    | –           |
|    | –           |
|   | –           |
|  | –           |
| <b>Hg</b>   | 2.5 mg      |
|  | A           |
|  | 9 kWh/1000h |

