



Digital AOS ABS Caliper 0-200mm, Blade, w/o Data Output Item number: 500-182-30



Description

This digimatic caliper allows you to take reliable measurements and offers you the following benefits:

- AOS (Advanced Onsite Sensor) induction type encoder used in top-of-the-line ABS coolant-proof calipers
- Thanks to the adoption of the electromagnetic induction type ABS encoder, this caliper can be used without concern for contamination on the scale face during measurement. Detection signal is not affected by dirt (water, oil, etc.) on surface of a scale.
- The slider provides smooth, stable and comfortable operation.
- Character height: 9 mm (150 and 200 mm), 11 mm (300 mm)
- ABS (ABSOLUTE) scale requires no origin setting after power-on and has no limit to response speed.

Features

Depth bar:	flat
Data output:	No
Mass:	194 g
Digital step:	0.01 mm
Max. response speed:	Unlimited
Battery life:	Appr. 5 years under normal use
ORIGIN (ABS-Zero):	Yes
ON/OFF:	Yes
ZERO/ABS:	Yes
Low voltage alarm:	Yes

Dimensions



Privacy settings

This site uses third-party website tracking technologies to provide and continually improve our services, and to display advertisements according to users' interests. I agree and may revoke or change my consent at any time with effect for the future.

ACCEPT ALL AND PROCEED

[Information & Settings](#)

Suggested retail price: **49.00 €***



Depth Base Attachment for Caliper
100mm width for 100, 150, 200mm Range
050084-10

Suggested retail price: **55.00 €***

Spare parts

Consumable spares:



Battery SR44 1.5V
938882

Privacy settings

This site uses third-party website tracking technologies to provide and continually improve our services, and to display advertisements according to users' interests. I agree and may revoke or change my consent at any time with effect for the future.

ACCEPT ALL AND PROCEED

[Information & Settings](#)