

BMP®21-PLUS Label Printer

BradyID.com/bmp21plus

TOUGH on
the Outside.
SMART on
the Inside.

The BMP®21-PLUS portable label printer takes on the toughest labeling jobs in the field. Whether you're in a server room, servicing a breaker box or organizing your workplace, you can count on the BMP®21-PLUS labeler to get the job done. And get it done quickly. With smart automatic formatting, all you need to do is drop a label cartridge in, type and print. Simple.

Extremely rugged and durable

- Drop tested printer, super rugged with molded rubber bumpers for fall protection.
- Long life rechargeable lithium-ion battery (*Included with BMP21-PLUS-KIT1, not included with BMP21-PLUS*)
- Ergonomic, center balanced printer with grab and go ridges grip for easy handling
- Heavy-duty magnet accessory and lanyard for hands free printing

Easy to use

- 2 line LCD display provides clear visibility
- ABC keypad, graphics library, hot keys and menu functions for fast label creation
- Smart Cell technology for automatic label set up and automatic formatting for wire wraps, terminal blocks, patch panels, cable flags and general labels
- Multi-functional accessory with magnet, flashlight and retractable printer stand for easy handling

Engineered Long Lasting Material Quality

- Prints durable true-sized 0.25 – 0.75 inch wide identification to maximize amount of data
- Adjustable length labels using the high performance continuous material
- Fulfill your requirements with up to 8 different industry specified materials that last

BMP®21-PLUS Printer

Catalog #	Description
BMP21-PLUS	BMP21-PLUS Printer*
BMP21-PLUS-KIT1	BMP21-PLUS Printer Kit**
BMP21-MAGNET	Magnet Attachment
BMP21-TOOL	Multi-Functional Tool
M-AC-110937	AC Power Adapter
BMP21-PLUS-BATT	Li-ION Battery Pack
BMP21-PLUS-HC	Hard Case



BMP21-PLUS Printer Kit shown.

* Printer includes label cartridge, lanyard and quick start guide (battery sold separately).

** Printer kit includes: printer, label cartridge, Li-ION battery, AC power / charger, hard case, lanyard and quick start guide.

US Patent Nos. 8,322,936; 8,846,171.

For more information, visit BradyID.com/bmp21plus.

Indoor/Outdoor Vinyl (B-595)



- 8-10 years average outdoor label durability
- Adheres to irregular and rough surfaces
- Stands up to grease, oil and most industrial chemicals

Catalog #	Color	Width Inch (mm)	Length Feet (m)
M21-250-595-WT	* BK on WHT	0.250 (6.35)	21 ft (6.40 m)
M21-375-595-WT	BK on WHT	0.375 (9.53)	21 ft (6.40 m)
M21-500-595-WT	BK on WHT	0.500 (12.70)	21 ft (6.40 m)
M21-750-595-WT	BK on WHT	0.750 (19.05)	21 ft (6.40 m)
M21-250-595-YL	* BK on YL	0.250 (6.35)	21 ft (6.40 m)
M21-375-595-YL	BK on YL	0.375 (9.53)	21 ft (6.40 m)
M21-500-595-YL	BK on YL	0.500 (12.70)	21 ft (6.40 m)
M21-750-595-YL	BK on YL	0.750 (19.05)	21 ft (6.40 m)
M21-375-595-OR	BK on OR	0.375 (9.53)	21 ft (6.40 m)
M21-500-595-OR	BK on OR	0.500 (12.70)	21 ft (6.40 m)
M21-750-595-OR	BK on OR	0.750 (19.05)	21 ft (6.40 m)
M21-375-595-BK	WHT on BK	0.375 (9.53)	21 ft (6.40 m)
M21-500-595-BK	WHT on BK	0.500 (12.70)	21 ft (6.40 m)
M21-750-595-BK	WHT on BK	0.750 (19.05)	21 ft (6.40 m)
M21-375-595-RD	WHT on RD	0.375 (9.53)	21 ft (6.40 m)
M21-500-595-RD	WHT on RD	0.500 (12.70)	21 ft (6.40 m)
M21-750-595-RD	WHT on RD	0.750 (19.05)	21 ft (6.40 m)
M21-375-595-BL	WHT on BL	0.375 (9.53)	21 ft (6.40 m)
M21-500-595-BL	WHT on BL	0.500 (12.70)	21 ft (6.40 m)
M21-750-595-BL	WHT on BL	0.750 (19.05)	21 ft (6.40 m)
M21-375-595-BR	WHT on BR	0.375 (9.53)	21 ft (6.40 m)
M21-500-595-BR	WHT on BR	0.500 (12.70)	21 ft (6.40 m)
M21-750-595-BR	WHT on BR	0.750 (19.05)	21 ft (6.40 m)
M21-375-595-GN	WHT on GR	0.375 (9.53)	21 ft (6.40 m)
M21-500-595-GN	WHT on GR	0.500 (12.70)	21 ft (6.40 m)
M21-750-595-GN	WHT on GR	0.750 (19.05)	21 ft (6.40 m)
M21-375-595-PL	WHT on PL	0.375 (9.53)	21 ft (6.40 m)
M21-500-595-PL	WHT on PL	0.500 (12.70)	21 ft (6.40 m)
M21-750-595-PL	WHT on PL	0.750 (19.05)	21 ft (6.40 m)
M21-375-595-GY	BK on Grey	0.375 (9.53)	21 ft (6.40 m)
M21-500-595-GY	BK on Grey	0.500 (12.70)	21 ft (6.40 m)
M21-750-595-GY	BK on Grey	0.750 (19.05)	21 ft (6.40 m)

* Cartridge is only compatible with the BMP@21-PLUS printer.

PermaSleeve® Heat Shrink Wire Markers



- 3:1 heat shrinkable ratio, wire marker sleeve
- Fade-resistant, flame-retardant, and superior aesthetic appearance

Catalog #	Color	Supplied Dia. Inch (mm)	Length Feet (m)	Approx. Wire Gauge
B-342 Heat Shrink Polyolefin Sleeve				
M21-125-C-342	* BK on WHT	0.125 (3.2)	7 ft (2.13 m)	22-16
M21-187-C-342	BK on WHT	0.187 (4.9)	7 ft (2.13 m)	20-10
M21-250-C-342	BK on WHT	0.250 (6.9)	7 ft (2.13 m)	16-8
M21-375-C-342	BK on WHT	0.375 (10.7)	7 ft (2.13 m)	12-4
M21-125-C-342-YL	*BK on YL	0.125 (3.2)	7 ft (2.13 m)	22-16
M21-187-C-342-YL	BK on YL	0.187 (4.9)	7 ft (2.13 m)	20-10
M21-250-C-342-YL	BK on YL	0.250 (6.9)	7 ft (2.13 m)	16-8
M21-375-C-342-YL	BK on YL	0.375 (10.7)	7 ft (2.13 m)	12-4

* Not compatible with ID PAL™ printer.

Polyester Labels for Component Marking



- High performance polyester material
- Best for flat, smooth surfaces
- B-488 is a solvent-resistant material

Catalog #	Color	Width Inch (mm)	Length Feet (m)
B-423 Polyester			
M21-250-423	* BK on WHT	0.250 (6.35)	21 ft (6.40 m)
M21-375-423	BK on WHT	0.375 (9.53)	21 ft (6.40 m)
M21-500-423	BK on WHT	0.500 (12.70)	21 ft (6.40 m)
M21-750-423	BK on WHT	0.750 (19.05)	21 ft (6.40 m)
B-430 Polyester			
M21-250-430	* BK on Clear	0.250 (6.35)	21 ft (6.40 m)
M21-375-430	BK on Clear	0.375 (9.53)	21 ft (6.40 m)
M21-500-430	BK on Clear	0.500 (12.70)	21 ft (6.40 m)
M21-750-430	BK on Clear	0.750 (19.05)	21 ft (6.40 m)
M21-250-430-WT-CL	* WHT on Clear	0.250 (6.35)	21 ft (6.40 m)
M21-375-430-WT-CL	WHT on Clear	0.375 (9.53)	21 ft (6.40 m)
M21-500-430-WT-CL	WHT on Clear	0.500 (12.70)	21 ft (6.40 m)
M21-750-430-WT-CL	WHT on Clear	0.750 (19.05)	21 ft (6.40 m)
B-488 Polyester			
M21-375-488	BK on WHT	0.375 (9.53)	21 ft (6.40 m)
M21-500-488	BK on WHT	0.500 (12.70)	21 ft (6.40 m)
M21-750-488	BK on WHT	0.750 (19.05)	21 ft (6.40 m)

* Cartridge is only compatible with the BMP@21-PLUS printer.

Self-Laminating Wire & Cable Wraps



- Clear, wrap-around tail overlaminates white print-on area to protect text
- Great for data cables or wires that are frequently handled & moved

Catalog #	Color	Width Inch (mm)	Length Feet (m)	Printable Height Inch (mm)
B-427 Self-Laminating Vinyl				
M21-750-427	*BK on WHT	0.75 (19.05)	14 ft (4.27 m)	0.375 (9.53)
M21-1000-427	*BK on WHT	1.00 (25.40)	14 ft (4.27 m)	0.375 (9.53)
M21-1250-427	*BK on WHT	1.25 (30.48)	14 ft (4.27 m)	0.50 (12.70)
M21-1500-427	*BK on WHT	1.50 (38.10)	14 ft (4.27 m)	0.50 (12.70)

* Not compatible with ID PAL™ printer.

Wire & Cable Wrap Arounds



- Nylon cloth label is highly pliable conforming to tightly curved surfaces
- Text auto-repeats when in wire marker mode

Catalog #	Color	Width Inch (mm)	Length Feet (m)
B-499 Nylon Cloth			
M21-375-499	BK on WHT	0.375 (9.53)	16 ft (4.88 m)
M21-500-499	BK on WHT	0.500 (12.70)	16 ft (4.88 m)
M21-750-499	BK on WHT	0.750 (19.05)	16 ft (4.88 m)

Terminal Blocks and Patch Panels Strips



- Narrow nylon cloth label strips for alignment on terminal blocks and patch panels
- Prints with user-specified spacing when using terminal block or patch panel modes

Catalog #	Color	Width Inch (mm)	Length Feet (m)
For Terminal Blocks			
M21-375-499-TB	BK on WHT	0.375 (9.53)	16 ft (4.88 m)
M21-500-499-TB	BK on WHT	0.500 (12.70)	16 ft (4.88 m)
For Patch Panels			
M21-375-499	BK on WHT	0.375 (9.53)	16 ft (4.88 m)
M21-500-499	BK on WHT	0.500 (12.70)	16 ft (4.88 m)

For more information, visit
BradyID.com/bmp21plus.

BRADY
WHEN PERFORMANCE MATTERS MOST™