

32GN500-B

LG UltraGear™ 32GN500-B 32-inch Gaming Monitor

EAN CODE: 8806091068996

31.5"

- NVIDIA® G-SYNC® Compatible
- AMD FreeSync Premium
- 165Hz Refresh Rate
- 1ms Motion Blur Reduction
- Black Stabiliser



For more information
www.lg.com/uk/monitors

DISPLAY

Size	31.5"
Resolution	1920 x 1080
Panel Type	VA
Aspect Ratio	16:9
Pixel Pitch	0.36375 x 0.36375 mm
Brightness	240cd/m² (Min.) 300cd/m² (Typ.)
Colour Gamut (Typ.)	sRGB 95% (CIE1931)
Colour Depth (Number of Colours)	16.7M
Contrast Ratio	1800:1 (Min.) 3000:1 (Typ.)
Response Time	5ms (GtG at Faster), 1ms MBR
Viewing Angle (CR≥10)	178° (R/L), 178° (U/D)
Curved	NO

SPEAKER

Type	NO
Audio output (watt)	N/A
Others	NO

POWER

Type	External Power(Adapter)
AC Input	100-240Vac, 50/60Hz
Power Consumption (Typ.)	40W
Power Consumption (Max.)	40W
Power Consumption (Sleep Mode)	Less than 0.5W
Power Consumption (DC Off)	Less than 0.3W

CONNECTIVITY

D-Sub	NO
D-Sub (Max. Resolution at Hz)	N/A
DVI	NO
DVI (Max Resolution at Hz)	N/A
HDMI	YES(2ea)
HDMI (Max. Resolution at Hz)	1920 x 1080 8bit @ 165Hz
DisplayPort	YES (1ea)
DP Version	1.4
DP (Max. Resolution at Hz)	1920 x 1080 8bit @ 165Hz
Mini DisplayPort	NO
mDP (Max. Resolution at Hz)	N/A
Thunderbolt	NO
Thunderbolt (USB-C Compatibility)	NO
Thunderbolt (Max. Resolution at Hz)	N/A
Thunderbolt (Data Transmission)	NO
Thunderbolt (Power Delivery)	N/A
USB-C	NO
USB-C (DP Alternate Mode)	NO
USB-C (Data Transmission)	NO
USB-C (Power Delivery)	N/A
Daisy Chain	NO
USB Upstream Port	NO
USB Downstream Port	NO
Audio In	NO
Mic In	NO
Headphone Out	YES
Line Out	NO

32GN500-B

LG UltraGear™ 32GN500-B 32-inch Gaming Monitor

EAN CODE: 8806091068996

31.5"

KEY FEATURES

- NVIDIA® G-SYNC® Compatible
- AMD FreeSync Premium
- 165Hz Refresh Rate
- 1ms Motion Blur Reduction
- Black Stabiliser

For more information
www.lg.com/uk/monitors

PRODUCT FEATURES

FEATURES

HDR 10	YES
VESA DisplayHDR™	NO
HDR Effect	YES
Nano IPS™ Technology	NO
Wide Colour Gamut	NO
Colour Calibrated	NO
HW Calibration	NO
Auto Brightness	NO
Flicker safe	YES
Reader Mode	YES
Colour Weakness	NO
Super Resolution+	NO
Motion Blur Reduction Tech.	MBR
NVIDIA G-Sync™	G-Sync Compatible
AMD FreeSync™	YES (Premium)
FreeSync	YES
Black Stabilizer	YES
Dynamic Action Sync	YES
Crosshair	YES
Auto Input Switch	NO
Sphere Lighting	NO
PIP	NO
Smart Energy Saving	YES

COLOUR

Front	Black
B/Cover	Black / Red
Stand	Black / Red
Base	Black / Red
Others	N/A



MECHANICAL

Display Position Adjustments	Tilt
Wall Mountable	100 x 100 mm

SIZE (MM)

Set (with Stand)	714.7 x 515.1 x 224.8
Set (without Stand)	714.7 x 428 x 77.5
Box	793 x 149 x 516
Wall Mount size (mm)	100 x 100

WEIGHT (KG)

Set (with Stand)	5.9
Set (without Stand)	5.2
Box	8.2

ACCESSORY

D-Sub	NO
DVI-D	NO
HDMI	NO
Display Port	YES
mDP to DP	NO
Thunderbolt	NO
USB Type C	NO
USB Type C to A Gender	NO
USB A to B	NO
USB3.0 Upstream Cable	NO
PC Audio	NO
Remote Controller	NO
Others (Accessory)	N/A