



FIBER TOOLS

FAST, ACCURATE AND RELIABLE FIBER CLEAVING

915CL OPTICAL FIBER CLEAVER

SPLICE AND CLEAVE FIBER THE RIGHT WAY!

FAST

Cleaved Fiber remains in the adapter ready to splice and is compatible with the 915FS, FSP200 or the 910FS fusion splicers.

ACCURATE

Precision-engineered blades accurately cleave fibers for minimal loss.

RELIABLE

Field tested to perform the dust bin safely collects end cuts.



Renewed Vision. Innovation Forward.

TempoCom.com | tel 800.642.2155

915CL

OPTICAL FIBER CLEAVER

BENEFITS

- Accurate Cleaves. Cleave multi-mode and single-mode fiber optic cables.
- Long Life. Blades rotate for longer life - over 48,000 cleaves.
- Adaptable. Supports 250um, 900um fibers and loose tube fibers.
- Fast. For use with the 915FS, FSP200 or the 910FS Optical Fusion Splicer for maximum speed and efficiency with auto return mechanism.
- Dust bin. Safely collects end cuts during cleaving process.
- Fixed Clamp. Allows the technician to use the 915CL as a standalone cleaver.

SPECIFICATIONS:

APPLICABLE FIBERS:	SM (G.652); MM (G.651); DS (G.653); NZDS (G.655); BIF (G.657)
FIBER CLEAVED LENGTH	10mm
CLADDING DIAMETER:	125µm
COATING DIAMETER:	0.25 mm and 0.9 mm
FIBER COUNT:	Single
CLEAVING ANGLE:	< 1.5°
BLADE LIFE	48,000 Cleaves
WEIGHT	0.56 lbs (255 g)
DIMENSIONS (HXWXD)	2.29 x 2.17 x 1.89" (58 x 55 x 48 mm)

ORDERING INFORMATION:

CAT. NO.	DESCRIPTION
915CL	915CL Optical Fiber Cleaver
01640	Cleaving Wheel
01332	250µm Adapter (Pair)
01333	900µm Adapter (Pair)
05801	Loose Tube Adapter (Pair)
03245	3mm Adapter (Pair)
PA1171	ProGrip 5-in-1 Fiber Optic Stripper



915FS

FOR USE WITH THE 915FS, FSP200 OR 910FS FUSION SPLICERS

CAT. NO.	DESCRIPTION
PA1177	ProGrip 3-in-1 Fiber Optic Stripper
10997	Economy Fiber Optic Stripper
PA1511	Kevlar Cutter
MSS100	Mid Span Slitter
07111	Fixed Clamp for 915CL with Screw
04268	Replacement Screw for Fixed Clamp

The 915CL is supplied with a fixed clamp and a mounting screw that the technician can use to permanently mount the fixed clamp to the cleaver. Shipped not assembled.

1390 Aspen Way Vista, CA • 92081

TC6580 12/19

Latin America Phone : 1.760.510.0558 | EMEA Phone: +44 (0) 1633 927 050

©2019 Tempo Communications, Inc. • An ISO 9001 Company

EMEA Address: Tempo Europe Limited • Brecon House, William Brown Close, Cwmbran • NP44 3AB, UK

TempoCom.com | tel 800.642.2155



Renewed Vision. Innovation Forward.



Follow us on Social Media
@TempoComms