

## TECHNICAL DATA SHEET

Part#: 40-SE

Hemostats - 8" 30°Curved - SS

Ideal for clamping parts for inspection

The 40-SE stainless steel locking hemostat with 30°curved serrated jaws is clean room safe. The overall length is 8".

|                       |                |
|-----------------------|----------------|
| • Precision Level     | ★★             |
| • Material            | SS (AISI 440)  |
| • Surface Resistivity | Conductive     |
| • Shape               | Curved         |
| • Tip Size            |                |
| • Tip Angle           | 30°            |
| • Tip Length          |                |
| • Body Width          | .283" (7.08mm) |
| • Body Height         | .06" (1.5mm)   |
| • OAL                 | 8" (200 mm)    |
| • Weight (OZ)         | 2              |
| • UPC                 | 662847010736   |
| • Schedule B          | 9018.90.80.00  |
| • ECCN                | EAR99          |
| • UNSPSC Code         | 42151685       |
| • Country of Origin   | Pakistan       |
| • Group               | Curved         |

