

## TECHNICAL DATA SHEET

Part#: 35PH

---

Hemostats - 5" Straight - SS - Vinyl-Coated Handle  
Ideal for clamping parts for inspection

The 35PH stainless steel locking hemostat with straight serrated jaws has vinyl-coated handles. The overall length is 5".

|                       |                          |
|-----------------------|--------------------------|
| • Precision Level     | ★★                       |
| • Material            | SS (AISI 440)            |
| • Surface Resistivity | Insulative               |
| • Shape               | Straight                 |
| • Tip Size            |                          |
| • Tip Angle           | Straight                 |
| • Tip Length          |                          |
| • Body Width          | 0.26" (6.5mm)            |
| • Body Height         | 0.183" (4.58mm)          |
| • OAL                 | 5" (125mm)               |
| • Weight (OZ)         | 2                        |
| • UPC                 | 662847003813             |
| • Schedule B          | 9018.90.80.00            |
| • ECCN                | EAR99                    |
| • UNSPSC Code         | 42151685                 |
| • Country of Origin   | Pakistan                 |
| • Group               | Straight - Vinyl Handles |

