

PRODUCT-DETAILS

ESP13.5-12B-LN

PG13.5 EURO INDEX CG BLACK SIZE2,



Product image
not available

General Information

Extended Product Type	ESP13.5-12B-LN
Product ID	7TCA296250R0123
EAN	5016947006178
Catalog Description	PG13.5 EURO INDEX CG BLACK SIZE2,
Long Description	Euro Index Cable Gland, PG13.5 Thread, 6.0-12.0mm Cable Range, 27.0mm Gland Depth, 27.0mm Gland Diameter, 24mm Across Flats Dimension, 100 Piece Pack, Polyamide 6.6 with Nitrile Rubber Seal, Black with Locknut

Ordering

EAN	5016947006178
Customs Tariff Number	8547200000

Dimensions

Product Net Weight	.03 lb
	13.605 g

Container Information

Package Level 2 Units	100 piece
Package Level 2 Width	1 in
	25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	Provide Strain Relief and Connection for Conduit Systems
Brand / Label	Adaptaflex
Color	Black
Insulation Material	IP68
Material	Polyamide/Nylon 6.6 with Nitrile Rubber Seal
Number of Batteries	0
Product Name	ADAPTAFLEX
Product Type	Euro Index Cable Gland with Locknut
Size	PG13.5
Special Functions	Integral claw design prevents cable twisting during installation
Temperature Range	-20 to +90 °C
UPC	786210262369

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	ESP13.5-12B-LN
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	ESP13.5-12B-LN

Classifications

ETIM 6	EC000441 - Cable screw gland
ETIM 7	EC000441 - Cable gland
UNSPSC	39121431
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4601 >> Cable gland connector

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image
not available