

[Home](#) ▶ [Products](#) ▶ [Accessories](#) ▶ **Probes**

Fluke 80PK-10 Pipe Clamp Temperature Probe

(0) [Write a review](#)[Buy now](#)

Key features

- Type-K thermocouple for fast temperature and superheat measurements of pipe surfaces

- For pipe diameters: 32 mm to 64 mm (1.25 in to 2.5 in)
- Measurement range: -29 °C to 149 °C (-20 °F to 300 °F)
- Measurements are repeatable to 0.56 °C (1 °F)
- Durable ribbon sensor
- 1 m (39 in) lead
- One year warranty

[⤴ Read less](#)

 [Manuals](#)

Product overview

Models

Reviews

Resources

Compatible products

Product overview: Fluke 80PK-10 Pipe Clamp Temperature Probe

Type K, extra large thermocouple clamps securely to larger pipes for fast temperature and superheat measurement.

About Fluke

[About us](#)

[Careers](#)

[Press](#)

[Supplier handbook](#)

Contact us

[Contact us](#)