

# DIGITAL MULTIMETERS

MEASURES VOLTAGE, AMPERAGE, RESISTANCE AND CONTINUITY



- Four new Multimeters
- cULus, CE, UKCA and RCM Listed
- CAT IV 600V, CAT III 1000V for 1000V models  
CAT III 600V for 600V models
- Backlit displays
- IP52 Ingress protection (61-357 & 61-347)
- 2M drop protection (61-357 & 61-347); 1M drop protection (61-337 & 61-327)
- Lead Warning and Fuse Notification (61-357, 61-347 & 61-337)



### 61-357

1000V Auto Range TRMS  
6000 Count Display Multimeter w/  
NCVT, Temp, Bar Graph & LoZ  
CAT IV 600V | CAT III 1000V



### 61-347

1000V Auto Range TRMS  
6000 Count Display  
Multimeter w/NCVT, & Temp  
CAT IV 600V | CAT III 1000V



### 61-337

600V Auto Range  
Multimeter w/NCVT & Temp  
CATIII 600V



### 61-327

600V Manual Range  
Multimeter w/ NCVT CATIII 600V



US LISTED







US LISTED



# DIGITAL MULTIMETERS

MEASURES VOLTAGE, AMPERAGE, RESISTANCE  
AND CONTINUITY

DIGITAL MULTIMETER SELECTION GUIDE	 NEW	 NEW	 NEW	 NEW
FOUR NEW MULTIMETERS	61-357	61-347	61-337	61-327
FEATURES				
CAT Rating (Safety)	CAT IV 600V CAT III 1000V	CAT IV 600V CAT III 1000V	CAT III 600V	CAT III 600V
Listing	cULus, CE, UKCA, RCM	cULus, CE, UKCA, RCM	cULus, CE, UKCA, RCM	cULus, CE, UKCA, RCM
Drop Protection	6.6 ft. (2m)	6.6 ft. (2m)	3.3 ft. (1m)	3.3 ft. (1m)
Ingress Protection	IP52	IP52	—	—
AC Voltage (Volts)	1000V	1000V	600V	600V
DC Voltage (Volts)	1000V	1000V	600V	600V
AC Current (Amps)	10A	10A	10A	—
DC Current (Amps)	10A	10A	10A	—
Ohms (Resistance)	60MΩ	60MΩ	40MΩ	4MΩ
AC Millivolts	6000	6000	4000	—
DC Millivolts	6000	6000	4000	4000
AC Milliamps	6000	6000	4000	—
DC Milliamps	6000	6000	4000	—
AC Microamps	6000	6000	4000	—
DC Microamps	6000	6000	4000	—
True RMS	✓	✓	—	—
High Voltage Alarm	ACV/DCV   >30V	ACV/DCV   >30V	ACV/DCV   >30V	ACV/DCV   >30V
Audible Continuity	✓	✓	✓	✓
Visual Continuity	✓	✓	✓	✓
Backlight	✓	✓	✓	✓
Temperature	-40 ~ 1832°F -40 ~ 1000°C	-40 ~ 1832°F -40 ~ 1000°C	-40 ~ 1832°F -40 ~ 1000°C	—
Low Impedance (LoZ)	✓	—	—	—
NCV	✓	✓	✓	—
Auto Ranging	✓	✓	✓	—
Range Hold	✓	✓	✓	—
Data Hold	✓	✓	✓	✓
Diode Test	✓	✓	✓	✓
Capacitance Test	6000 μF	6000 μF	4000 μF	—
Frequency / Duty Cycle	10Hz - 9.99 KHz	10Hz - 9.99 KHz	10Hz - 9.99 KHz	10Hz - 9.99 KHz
Max / Min	✓	✓	✓	—
Magnetic Strap Mount	✓	✓	✓	✓
Test Probe Holder	✓	✓	✓	✓
Auto-Power Off	✓	✓	✓	✓
APO Disable	✓	✓	✓	✓
Low Battery Indication	✓	✓	✓	✓
Battery Type (Included)	3 x 1.5V AAA	3 x 1.5V AAA	3 x 1.5V AAA	3 x 1.5V AAA
LCD Display Count	6000	6000	4000	2000
Lead Warning	✓	✓	✓	—
Fuse Notification	✓	✓	✓	—
Bar Graph	✓	—	—	—
Battery Test	—	—	—	✓
Warranty	2-Year*	2-Year*	2-Year*	2-Year*
Accessories				
Leads, Case & Temp. Sensor	Included	Included	Included	Leads Only

\* Go to [idealind.com](http://idealind.com) for complete warranty information  
Specifications are subject to change without notice.

# ACCESSORIES



**TC-757**  
Thermocouple



**TL-757**  
Test Leads w/Alligator Clips  
For Use with: 61-357, 61-347, 61-337, 61-327



**UMHS-757**  
Universal Magnetic Hanging Strap  
For Use with: 61-357, 61-347, 61-337, 61-327



**C-357**  
Nylon Carrying Case  
For Use with: 61-357,  
61-347, 61-337, 61-327



**F-11A-347357**  
Fuse for 61-357 & 61-347



**F-600mA-347357**  
Fuse for 61-357 & 61-347



**F-10A-337**  
Fuse for 61-337



**F-400mA-337**  
Fuse for 61-337



Scan this QR code  
with your smartphone  
to learn more about  
the testers.



IDEAL INDUSTRIES, INC.

IDEAL INDUSTRIES EMEA

Unit 3, Europa Court, Europa Boulevard, Warrington, WA5 7TN, UK | +44 (0)1925 444 446 | eur.sales@idealindustries.com

International offices:

Australia • Canada • China • India • Germany • Mexico • Middle East • UK

For complete sales office contact information, visit us at:

[www.idealind.com](http://www.idealind.com)

