
**NON-CONTACT VOLTAGE TESTERS** 

DETECT PRESENCE OF AC VOLTAGE

- Four new NCVT's
- · CE, UKCA and UL Listed
- · CAT IV 1000V AC & CAT IV 600V AC models
- · Dual and Single Range Models
- · IP67 Dust Tight/Water Immersion Protection\* (61-657 & 61-647)
- 2 Meter drop protection (61-657 & 61-647)
- Bright LED forward facing torch (3 models)





\*Protection against the effects of water immersion in water between 5.9 in. (15cm) and 39.37 in. (1m) for 30 minutes.



## **NON-CONTACT VOLTAGE TESTERS**

## DETECT PRESENCE OF AC VOLTAGE

NON-CONTACT VOLTAGE TESTER SELECTION GUIDE FOUR NEW NCVTS	NEW	NEW	NEW	NEW
FEATURES	61-657	61-647	61-637	61-627
CAT Rating (Safety)	CAT IV 1000V	CAT IV 1000V	CAT IV 600V	CAT IV 600V
Listing	cULus, CE, UKCA, RCM			
Voltage Sensing Range	12 ~ 1000V AC	50 ~ 1000V AC	24 ~ 600V AC	50 ~ 600V AC
Dual Range	<b>✓</b>	_	_	_
Torch	<b>✓</b>	<b>✓</b>	<b>✓</b>	_
Drop Protection	6.6 ft. (2m)	6.6 ft. (2m)	3.3 ft. (1m)	3.3 ft. (1m)
Ingress Protection	IP67	IP67	_	_
Dual Range Sensitivity	<b>✓</b>	_	_	_
Audible Indication	<b>✓</b>	<b>✓</b>	<b>✓</b>	<b>✓</b>
Audible Disable	<b>✓</b>	<b>V</b>	<b>✓</b>	_
Visual Indication	Green On, Flashing Red	Green On, Flashing Red	Green On, Flashing Red	Green On, Flashing Red
Visual Range Indicator	Blue Low, Red High	_	_	_
Lanyard Compatible	<b>✓</b>	<b>✓</b>	<b>✓</b>	<b>✓</b>
Auto-Power Off (APO)	<b>✓</b>	<b>✓</b>	<b>✓</b>	<b>✓</b>
Low Battery Indication	<b>✓</b>	✓	✓	<b>✓</b>
Battery Type	2 x 1.5V AAA			
Warranty	2-Year*	2-Year*	2-Year*	2-Year*

<sup>\*</sup> Go to idealind.com for complete warranty information

Specifications are subject to change without notice.



Scan this QR code with your smartphone to learn more about the testers.



**Detects AC voltage at outlets** (including TR's w/61-657)



**Detects AC voltage** on conductors



**Detects AC voltage** at panels



2 x 1.5 AAA Batteries (Included)



Unit 3, Europa Court, Europa Boulevard, Warrington, WA5 7TN, UK | +44 (0)1925 444 446 | eur.sales@idealindustries.com