


► General data



Plug component, nominal current: 8 A, rated voltage: 160 V, pitch: 3.5 mm, no. of positions: 5, type of connection: Screw connection

Order number	1840395
Type	MC 1,5/ 5-ST-3,5

Barcode number	4017918111571
Unit pack	50 Pcs.
Customs tariff	85369010000

► Technical data

Dimensions / positions

Height	11.1 mm
Pitch	3.5 mm
Dimension a	14 mm
Number of positions	5
Screw thread	M 2
Tightening torque	0.22 Nm

Technical data

Insulating material group	I
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/2)	160 V
Rated voltage (II/2)	320 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	8 A
Nominal voltage U_N	160 V
Nominal cross section	1.5 mm ²
Maximum load current	8 A (with 1.5 mm ² conductor cross section)
Insulating material	PA
Inflammability class acc. to UL 94	V0
Internal cylindrical gage	A 1
Stripping length	7 mm

Connection data

Min. conductor cross section, rigid	0.14 mm ²
Conductor cross section, rigid max.	1.5 mm ²
Conductor cross section flexible min.	0.14 mm ²
Max. conductor cross section, flexible	1.5 mm ²
Min. conductor cross section, flexible, with ferrule with plastic sleeve	0.25 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve max.	1.5 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve min.	0.25 mm ²
Max. conductor cross section, flexible, with ferrule with plastic sleeve	0.5 mm ²
Min. conductor cross section AWG/kcmil	28
Conductor cross section AWG/kcmil max	16
2 conductors with same cross section, solid min.	0.08 mm ²
2 conductors with same cross section, solid max.	0.5 mm ²
2 conductors of the same cross section, flexible, min.	0.08 mm ²
2 conductors with same cross section, flexible max.	0.75 mm ²
2 conductors of the same cross section, flexible, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with identical cross section, flexible, ferrules with plastic sleeve, max.	0.34 mm ²
2 conductors of the same cross section, flexible, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with identical cross section, flexible TWIN ferrules with plastic sleeve, max.	0.5 mm ²

► Certificates

UL




Nominal voltage U_N	300 V
Nominal current I_N	8 A
AWG/kcmil	30-14

CSA


Comments	all numbers of positions are accepted
Nominal voltage U_N	300 V
Nominal current I_N	8 A
AWG/kcmil	28-16

▸ Drawings

Diagram



Dimensioned drawing



Approval logo



► Accessories

Item	Designation	Description
General		
1834372	KGK-MC 1,5/ 5	Cable housing, for cable diameters of up to 8.5 mm, cable ties and marker strips are included, color: green, no. of positions: 5
<hr/>		
Marking		
0804073	SK 3,5/2,8:FORTL.ZAHLEN	Marker card, printed horizontally, self-adhesive, 10-section marker strip, 14 identical decades marked 1-10, 11-20 etc. up to 91-100, sufficient for 140 terminal blocks
<hr/>		
Tools		
1205037	SZS 0,4X2,5	Screwdriver, bladed, matches all screw terminal blocks up to 1.5 mm ² connection cross section, blade: 0.4 x 2.5 mm
<hr/>		

► Additional products

Item	Designation	Description
General		
1897128	EMC 1,5/ 5-G-3,5	Header, nominal current: 8 A, rated voltage: 160 V, pitch: 3.5 mm, no. of positions: 5, mounting: press in
1911046	EMCV 1,5/ 5-G-3,5	Header, nominal current: 8 A, rated voltage: 160 V, pitch: 3.5 mm, no. of positions: 5, mounting: press in
1844249	MC 1,5/ 5-G-3,5	Header, nominal current: 8 A, rated voltage: 160 V, pitch: 3.5 mm, no. of positions: 5, mounting: Soldering
1843635	MCV 1,5/ 5-G-3,5	Header, nominal current: 8 A, rated voltage: 160 V, pitch: 3.5 mm, no. of positions: 5, mounting: Soldering

► Address

Phoenix Contact GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 3 00
Fax +49 5235 3 1200
<http://www.phoenixcontact.com>

© Phoenix Contact
Technical modifications reserved