

Ratchet wrench insulated for nut drivers 1/4" switchable (43054)



wiha 
Tools that work for you

Wiha Werkzeuge GmbH
Obertalstraße 3-7 78136 Schonach
E-Mail: info.de@wiha.com
Tel.: +49 (0)7722 959-0

Order no.: 43054

Article number: 246192

EAN: 4010995430542

Customs tariff number: 82041100

Protects your health: Reduction of the risk of injury by increasing the hand working space.

Offers you full protection: Each tool individually tested at 10,000 V AC and usable for 1,000 V AC.

Increases your flexibility: Adjustable right or left rotation through switching lever.

Dimensions: 145 x 58 x 32 mm

Application: Safe installation of terminals and sleeves, conductor connections and fastening of conductor lines. For working on live parts up to 1,000 V AC.

Safety is top priority when users are working on live parts. With the insulated ratchet wrench screws and bolts can be easily tightened or opened. The integrated switching lever allows effortless switching between right and left rotation. Furthermore, the ball fastener provides a secure hold for the inserted nut drivers, which can be interchanged by the simple pressing of the release button. The insulated ratchet wrench is subject to individual piece testing as per the international EN/IEC 60900 standard, thus ensuring safe work on live parts up to 1,000 V AC.

IEC 60900

Customs tariff number	82041100
-----------------------	----------

Blister pack	No
--------------	----

Hexagon head 1 (Inch)	1/4"
-----------------------	------

Overall length (mm)	145 mm
---------------------	--------

VDE article	No
-------------	----