

# **SMART DISPENSE 06**

Set DP H

The SMART DISPENSE 06 is a professional dispensing device for manual tasks where high precision and repeat accuracy are essential. These dispensers also allow heating the dispensing nozzle. A temperature sensor inside the dispensing pen measures the cartridge temperature. Temperature insulated dispensing pens are available for common cartridge sizes in order to prevent the material from heating up during the dispensing application.

When highly viscous materials are used, the viscosity setting can be adjusted in the dispensing pen via an optionally integrated nozzle heater. Furthermore, 1K material can be processed reliably, whether in liquid or paste form. For materials with a low viscosity, the formation of drops on the dispensing needle is prevented through a manual retract vacuum.

## **Top Features**

Controlled dispensing pressure.



## Fully electronic dispensing device

Compact format, innovative design,

Manual procedure

**Format** 



### Repeatability

A consistent volume can be dispensed with the volumetric dispensing device, regardless of the viscosity



#### **Temperature control**

Heatable dispensing nozzle for regulating temperature of the medium



#### **Plug and Play**

Intuitive operation through direct access to parameters such as pressure, time, temperature




#### Flexibility

Exact dispensing results for low to highly viscous materials through temperature regulation

# Standard equipment

intuitive software

- Control unit SMART DISPENSE 06
- Dispensing pen (size of choice) with integrated temperature sensor, nozzle heater and connecting cable (1.5m)
- Stand for dispensing pen, foot switch, needle set (27pcs)
- Pneumatic hose (d=6mm, l=5m)
- Power supply 90-230 V AC -> 24V DC
- USB cable
- Short instruction



#### **Technical details**

Cartridges to use:	3, 5, 10, 30 ccm
Viscosity range:	0.1-10 <sup>5</sup> mPas
Nozzle heater:	Max. 90°C
Communication:	USB 2 (Typ B)
Weight:	1,5 kg max
Size:	192 x 152 x 60 mm <sup>3</sup>

_		-	•		
"	n	٠	"	n	c
•	_			,,,	S

-  -	
Retract vacuum:	Manual

Line dispense settings:	Time range:	0,1s-999s
	Pressure level:	0,2 - 3,5 bar
Dot dispense settings:	Time range:	0,001s-2s(±0,0005s)
	Pressure range:	0,2 bar - 4,5 bar
	Repeatability:	5 % (Energiepuls)
	Smallest dispensing vol.:	2 nl

# SMART DISPENSE 06 DP H: Optional extras

	Article nr.	Name		
	Set variat	Set variations		
Heat S com	SD06.0202	SMART DISPENSE 06 Set DPH 5		
Heat 10 ccm	SD06.0203	SMART DISPENSE 06 Set DPH 10		
	Optional e	extras		
MARTIN'	SD06.0050	Vacuum module SD06		
<i>†</i> <b>1</b>	PD80.1011	Dispensing pen 3ccm		
<i>†</i> <b>1</b>	PD80.1012	Dispensing pen 5ccm		
<i>†</i> <b>1</b>	PD80.1013	Dispensing pen10ccm		
<i>†</i> <b>1</b>	PD80.1014	Dispensing pen 30ccm		
<b>A</b>	PD60.1012	Dispensing pen 5ccm with nozzle heating		
4	PD60.1013	Dispensing pen 10ccm with nozzle heating		
4	PD60.1014	Dispensing pen 30ccm with nozzle heating		
5	PD10.0012	Stand for dispensing pen for 3 & 5ccm cartridges		
5	PD10.0013	Stand for dispensing pen for 10ccm cartridges		
5	PD10.0014	Stand for dispensing pen for 30ccm cartridges		
_	PD91.0003	Foot switch for CD06/SD06		

More accessories and consumables at www.martin-smt.de