


**RoHS
Compliant**



Specifications

Connector to Connector	: 90° U.FL Plug to SMA Bulkhead Jack
Impedance	: 50Ω
Frequency Range	: DC to 3 GHz
Max. Working Voltage	: 60Vrms
Min. Dielectric Withstanding Voltage	: 200Vrms
Min. Insulation Resistance	: 500MΩ
Cable Length	: 3.9" (100mm)
Jacket Colour	: Black

Diagram



Specification Table

Item	Description
1	SMA B/H Jack for Ø1.37mm Cable (Nut × 1, Washer × 1)
2	Heat Shrink Tube F32 Ø2.5mm L = 15mm Colour : Black
3	Ø1.37mm Cable Colour : Black
4	U.FL-LP-088 Shell for Ø1.37mm Cable
5	U.FL-LP-088 Terminal for Ø1.37mm Cable

Part Number Table

Description	Part Number
90° U.FL Plug to SMA Bulkhead Jack, 50Ω, 100mm, Black	R-132G7210100CB

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro