



3
 JAHRE
 YEARS
 GARANTIE
 WARRANTY

ANSMANN Powerbank 10000mAh PB218 wireless

- Compact and handy Powerbank, which also has a Type C input and wireless output alongside the standard inputs and outputs. Capacity: 10000 mAh / 37 Wh
- Suitable for all smartphones and tablets that can be charged via a USB connection. Compatible with the Qi standard for wireless charging.
- Multi-Safe technology: Over-charging protection, deep discharge protection, overload protection and short-circuit protection
- Input: Micro USB USB type C - 5 - 9V DC / 2.4 A
- Output: 2× USB USB type C - 5 - 12V DC / 3 A
- Accessories: Micro-USB charge cable
- 3 year ANSMANN-Germany manufacturer's guarantee

INFORMATION

Product name	Powerbank 10000mAh PB218 wireless
Part No.	1700-0135
EAN-Code	4013674177783
Customs tariff number	85076000900
Product content	Powerbank, micro-USB cable, operating instructions

Product	144,5 × 69,5 × 15,5 mm / 0 g
Packing + Product	100 × 30 × 215 mm / 238 g
Packing Unit	40 (388 × 330 × 220 mm)

