

Page NP6 - 671940 Digital Edition

Basic HTML Version

[Table of Contents](#) | [View Full Version](#)

NEW PRODUCTS 2012

12V LIGHTED SNAP-IN ROUND ROCKER SWITCH

Current Rating:	20A-12VDC
Contact Resistance:	50m Ohm max
Insulation Resistance:	DC 500V 100M Ohm min.
Dielectric Strength:	AC 1500V for 1 minute
Body Material:	Nylon (UL 94V-2). Blue
Terminal Material:	Silver plated brass
Terminal Type:	12V Lead Wire Assembly

Part. No. Type Action Actuator

30-12340 SPST ON - OFF Blue LED
Illuminated body.
Red LED Rocker*

Mounting hole: 20.2mm (.79")

* Red LED illuminates when switch is in ON position

IN-LINE PUSH BUTTON SWITCH

Current Rating:	3A-125V
Contact Resistance:	30 Ohm max
Insulation Resistance:	100m Ohm min.
Terminal Type:	Solder

Sizes: Overall Length 3.3"
Body/handle Length 2.8"
O.D. .75"

Page NP5

No. 30-825
(Maximum cable O.D. 6.0mm)

0.10±0.2

71.5±0.7
85±1

12V ACCESSORIES

CIGARETTE LIGHTER PLUG WITH ON-OFF SWITCH

Current Rating:	8A-12VDC
Housing Material:	ABS (UL94-HB)
Contact Material:	Tip - Nickel Plated Brass Ground - Nickel Plated Steel
Switch:	SPST Rocker Switch with LED
Wire Size:	SPT-1 Type up to 18 AWG
Fuse:	8A Standard 3AG type (included)

No. 48-790

12V SOCKET TO 2 POSITION FLAT CONNECTOR

12V SOCKET TO 2 PIN CONNECTOR

This 10" long Adaptor has 2 position flat trailer harness connector on one end. On other end is standard 12V cigarette lighter socket. Allows 12V connection from 2 pin trailer connector.

No. 48-1276

This 4" long Adaptor has two pin connector on one end that connects with any of the 12V power supplies with interchangeable DC plugs feature. On other end is standard 12V cigarette lighter socket.

No. 48-1274

SPLASH PROOF HOLDER WITH LED INDICATOR LIGHT

IP66

Rating 20A 32V DC, holds 1/4"-1-1/4" 3AG type fuse. Can be used in panel up to 3/8" thick, mounts in .63" (16.0mm) mounting hole 94V UL material, LED indicates when fuse is blown.
No. 64-2015

IP66

Rating 20A 12V/24 V DC, holds standard blade type ATC fuse 14 AWG loop wire, LED indicates when fuse is blown.
No. 64-2020

NP6

OFC...,D,E,F,G,H,NP1,NP2,NP3,NP4,NP5

NP7,NP8,NP9,NP10,1,2,3,4,5,6,...352



Page NP5