Spade Terminals Vinyl-Insulated

pro-**Power**

RoHS

Compliant




Features

- Enable universal used with studs/screws to fix on equipment
- Fixing structure with an open-ended can be installed and removed without complete removal of the mounting screw

Specifications

Conductor Material	: Copper Brass
Insulation Material	: PVC
Plating	: Tin
Heat Resistant	: -10°C to +75°C

Diagram



Specification Table

Part Number	Wire Range mm² (AWG)	Stud Size (mm)	Colour	Dimension (mm)						Pack		
				d2	W	F	L	E	D	d1	Т	Size
STSV1-3.2	0.5-1.5 (22-16)	3 3.3 5.7 6.5 21	21									
STSV1-3.7		3.5	- Red	3.8	5.7	6.5	21	10	4.3	1.7	0.75	100
STSV1-4		4		4.4	6.4	6.5	21					
STSV1-5		5		5.4	8.1	6.5	21					
STSV2-3.7	1.5-2.5 (16-14)	3.5		3.8	5.7	6.5	21	10	4.8	2.3	0.8	
STSV2-5.0		5	Blue	5.4	8.1	6.5	21					
STSV2-6.0		6		6.6	9.3	6.5	21					

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands

Element14.com/exclusive-brands

